



SPECIFICATION SHEET

56-3185



ARMORTUFF® XT NITRILE DIPPED GLOVE WITH JERSEY LINER AND SMOOTH FINISH - KNIT WRIST

- Armor™ Series gloves feature a unique combination of low-coating deposit weight and high abrasion resistance and provide the wear of heavier, bulkier nitrile coated gloves without sacrificing flexibility and tactile sensitivity
- ActiFresh™ treated to reduce germs and odors
- Provides protection from physical hazards such as cut, puncture, snag and abrasion
- Blue nitrile coating on cotton jersey liner
- Comfortable and flexible; provides excellent dexterity and grip
- Palm coat provides flexibility and ventilation
- Knit wrist helps prevent dirt and debris from entering the glove
- Resistant to grease and oils

APPLICATIONS

- General assembly
- Assembly
- Fabrication
- Parts handling
- Maintenance

CARE INSTRUCTIONS

Use commercial laundry soap or detergent (do NOT use dry cleaning solutions) Wash in warm to medium hot water, do not exceed 104°F (40° C). Wash for 10 minutes and rinse in cold water. Repeat wash and rinse if soiling is especially heavy. Tumble dry - maximum temperature 140°F (60° C)

TECHNICAL DATA

MATERIAL	Nitrile, cotton			
COLOR	Shell: ■ Natural / Grip: ■ Blue			
CUFF STYLE	Knit Wrist			
SIZES	S - XL			
PACKAGING	12 pairs per dozen, 6 dozen per case			
CASE SIZE	10.6" x 10.6" x 15.7" / 27cm x 27cm x 40cm			
CASE WEIGHT	S	M	L	XL
	16.5 lbs 7.5 kg	17.2 lbs 7.8 kg	17.9 lbs 8.1 kg	19.4 lbs 8.8 kg
COO	Pakistan			

PERFORMANCE PROPERTIES

EN388: 4221						
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-

BARCODES

ITEM	BAG	DOZEN	CASE
■ 56-3185/XL	---	01616314034190	02616314034190
■ 56-3185/L	---	01616314034169	02616314034169
■ 56-3185/M	---	01616314034176	02616314034176
■ 56-3185/S	---	01616314034183	02616314034183



DIMENSIONS (in/cm)

	S	M	L	XL
A	10.4 / 26.5	10.8 / 27.5	11.2 / 28.5	11.6 / 29.5
B	4.6 / 11.7	4.8 / 12.1	5 / 12.8	5.5 / 13.9

Thickness: 0.55 +/- 0.165mm

