



SPECIFICATION SHEET

R5

PACIFIC R5 BRUSHFIRE/RESCUE HELMET

- Compliant with ANSI Z89.1
- Lightweight Dupont™ Kevlar® composite shell weighs less than composite fiberglass and composite alternatives
- Shell is not affected by UV exposure
- Composite resins offer higher temperature resistance (up to 600°F) without distorting or melting
- Ratchet headband with easy-to-adjust dial which accommodates a variety of head sizes (52-64cm)
- Scallop-sided shell designed to accommodate a variety of earmuffs
- Lightest weight helmet on the market
- 3-point polyester chin strap with quick-release buckle keeps helmet in place for rescue applications
- Neck protector (optional) for ear and neck protection
- Full range of tailored Decals/Badges/Reflectorising available
- Ear muff mounting clips (optional) for secure goggle fastening to helmet
- ESS mounts make goggle attachment quick and easy, even with gloves on
- Wildland NFPA 1977 - must purchase neck protector to meet standard

APPLICATIONS

- Wildland
- Rope Rescue
- High Angle
- Windfield
- Arborists
- EMT's
- Cave Rescue
- Window Washer

TECHNICAL DATA

MATERIAL	Outer Shell: Kevlar® composite / Inner Shell: Polyurethane
COLOR	<div style="display: flex; gap: 5px;"> <div style="width: 10px; height: 10px; background-color: blue; border: 1px solid black;"></div> Blue (854-6022) <div style="width: 10px; height: 10px; background-color: red; border: 1px solid black;"></div> Red (854-6020) <div style="width: 10px; height: 10px; background-color: white; border: 1px solid black;"></div> White (854-6023) </div>
SIZES	OSFA, Adjustable
PACKAGING	17 per case
CASE	26.5" x 23.5" x 13" / 67.3cm x 59.7cm x 33.0cm
CASE WEIGHT	19.72 lbs / 8.95
COO	New Zealand
HARM CODE	6506.10.6075

WARRANTY

6-year limited warranty

Each helmet also carries a 2-year limited warranty on impact liners and ratchet suspensions. Internal parts including crown pads, ribbons and sweatbands are NOT covered by this warranty.

BARCODES

ITEM	EACH	DOZEN	CASE
<div style="width: 10px; height: 10px; background-color: blue; border: 1px solid black;"></div> 854-6022	616314148958		02616314148956
<div style="width: 10px; height: 10px; background-color: red; border: 1px solid black;"></div> 854-6020	616314149122		02616314149120
<div style="width: 10px; height: 10px; background-color: white; border: 1px solid black;"></div> 854-6023	616314149160		02616314149168



DIMENSIONS (in/cm)

	OSFA				
A	11.4 / 29.0				
B	8.3 / 22.1				
C	5.9 / 15.0				

