


SW2009



Revision level		Revision Record	Changed	Date	Approved	Date
Drawing	Part					
04	-	SEE ECN# 011651	TJM	10/1/2010	TJM	10/01/2010



04

Material
PA66HS, PA66HIRHSUV

1.0 to 35.0	180	6.3-7.0	0.7-7.0
Bundle ϕ Range	Min Loop Tensile Strength (Newtons)	Mounting Hole Size	Panel Thickness Range
PERFORMANCE SPECIFICATIONS			

Units millimeters

Dimension without tolerances details to:

.xxxx = ± 0.0025
 .xxx = ± 0.013
 .xx = ± 0.13
 .x = ± 0.3
 None = ± 0.8
 $\angle$ = $\pm 0.5^\circ$

The copyright of this drawing is reserved by HellermannTyton. It is issued on condition that it is not reproduced, copied, or disclosed to a third party, either wholly or in part, without the consent of HellermannTyton.

Drawn	AAC	7/12/2010
Approved	TJM	10/01/2010
HellermannTyton North America Email: corp@htamericas.com Web: www.hellermann.tyton.com		

Article/Type-No	T50SOSFT6LGE	Scale	1:1
Title	T50SOSFT6LG-E T50S OUTSIDE SERRATED WITH FIR TREE	Project Number	PRP09-0334
Drawing-No	CT09-0334-003CST	Format	AH
Production : Phase		Sheet	1/1

Product Number
Cross Reference Record

Uncontrolled Document

Type Number	UNS Universal Number System	Customer Drawing Title
T50SOSFT6LGE(BLK)	157-00097	

Issued By:

HellermannTyton

Reference Drawing Number:

CT09-0334-003CST

Issue Date:

JULY 11,2013