



# SPECIFICATION SHEET

## 906-2080NOL7B

### FIRE RESISTANT HOOD

- Meets or exceeds the standards of NFPA 1971
- Highest quality knitted "sock" style hoods that provide protection from flash fire hazards with added 2-ply construction for thermal insulation in cold weather conditions
- Nomex® protective barrier carbonizes and thickens when exposed to the intense heat of today's fires. This increases the protective barrier to minimize burn injury. Stays supple and flexible till it's cool, which gives you valuable extra seconds of protection when needed most
- Garments made of Nomex® are also durable, lasting on average two to three times longer than other standard protective fabrics
- Lenzing FR® is a specialty viscose fiber, is flame resistant, and naturally derived from wood. It offers heat and flame protection and its unique thermal properties combined with permanent flame resistance makes it a "Heat Protection Fiber".
- This fabric combination provides comfort and breathability
- The most cost effective solution to your NFPA requirements

### APPLICATIONS

- Firefighting
- Chemical plants

### TECHNICAL DATA

|             |   |
|-------------|---|
| MATERIAL    | 20% Nomex® and 80% Lenzing FR®            |
| COLOR       | <input type="checkbox"/> White            |
| TPP RATING  | 17  |
| CUT         | Straight-Cut                              |
| COVERAGE    | Full Face                                 |
| LAYER       | Single w/ Bib                             |
| SIZES       | OSFM                                      |
| PACKAGING   | 1 per polybag / 12 hoods per case         |
| CASE        | 10" x 6" x 12" / 25.4cm x 15.2cm x 30.5cm |
| CASE WEIGHT | 1.4 kg                                    |
| COO         | USA                                       |

### BARCODES

| ITEM                                   | EACH         | CASE           |
|--|--------------|----------------|
| <input type="checkbox"/> 906-2080NOL7B | 616314156113 | 02616314156111 |



### DIMENSIONS (in/cm)

|          | OSFA         |  |  |  |  |  |  |
|----------|--------------|--|--|--|--|--|--|
| <b>A</b> | 16.1 / 40.9  |  |  |  |  |  |  |
| <b>B</b> | 18 / 45.7    |  |  |  |  |  |  |
| <b>C</b> | 15.25 / 38.7 |  |  |  |  |  |  |
| <b>D</b> | 9 / 22.9     |  |  |  |  |  |  |
| <b>E</b> | 9.75 / 24.8  |  |  |  |  |  |  |
| <b>F</b> | 10 / 25.4    |  |  |  |  |  |  |

