



PROTECTIVE INDUSTRIAL PRODUCTS

57-8675 Specification Sheet

COATED SUPPORTED GLOVES

PRODUCT DESCRIPTION:

Neoprene coated gloves, smooth, brushed interlock lined, 31-inch gauntlet.

- Neoprene gloves provide superior protection from a wide range of chemicals such as acids, caustics, solvents and oils.
- Etched rough finish styles have excellent non-slip grip and cut resistance.
- Multi-dip process provides fully liquid proof protection.
- Black color hides dirt.

Applications:

Ideal for refining, galvanizing, degreasing, plating, petrochemical industries and kitchen cleaning & maintenance.

TECHNICAL DATA:

Material: Neoprene

Construction: Neoprene over cotton

Color: Black

Cuff Style: Continuous

Available Sizes: Men's one size

Packaging: 12 pairs per case

Case Dimensions (cm) 50 x 35 x 35 (in) 19.7 x 13.8 x 13.8

Case Weight: 28.7 lbs / 13.0 kg

Manufacturer Certifications: ISO9001:2000 certified

Country of Origin/Harmonization Code: Sri Lanka/6116.10.6500

Laundering Instructions:

It is strongly advised not to wash and re-use these gloves when they are used to protect against chemical products.




DIMENSIONS:

Size Available	Men's one size
Over Length (cm) – A (in)	82.0 32.3
Palm Width (cm) – B (in)	12.0 3.8
Tolerance	+/- 0.5 cm
Thickness	0.65 - 0.75 mm (+/- 0.225mm)

CUT RESISTANCE PROPERTIES:

EN388: 3121

Abrasion	0	1	2	3	4	
Cut	0	1	2	3	4	5
Tear	0	1	2	3	4	
Puncture	0	1	2	3	4	



BARCODE #	DOZEN	CASE
57-8675	01616314002564	02616314002564

This document is the property of PIP and the information contained herein is proprietary to PIP.