



(.946)
COMPLETELY CLOSED
10 TEETH POSITIONS
"F" 03




$\phi .784 \pm .020$ 03
SEE NOTE 1
"A"

(1.398) 03
MAXIMUM OPENING
2 TEETH ENGAGED
"E"




$\phi .928 \pm .020$ 03
SEE NOTE 1
"B"

.234 $\pm$.010 03
"C"



(.010) RIB
(.011) RIB 03
"G"
.069 $\pm$.010 03
"D"

DETAIL A
SCALE 10 : 1



AS MOLDED
FULL SCALE

PRODUCT CODE DESCRIPTION

SNP18AGHS

COLOR
(CONSULT FACTORY FOR AVAILABLE COLORS)

03

INVENTORS	HellermannTyton®		
	ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANN TYTON		
	name	date	city, state

NOTES

- 1) INSIDE DIAMETERS ARE MEASURED IN THREE PLACES SPACED 120 DEGREES APART EXCLUDING RIB.
- 2) 16 TOTAL TEETH, 10 TEETH POSITIONS.

REVISION	level	03
	by	AAC
	date	04/20/2006
	ECN #	010409
	part level	A

DIMENSIONS	.XXXX = $\pm .0005$
	.XXX = $\pm .005$
	.XX = $\pm .01$
	.X = $\pm .03$
	$\angle = \pm 0.5^\circ$
unless otherwise specified	
units	inches

PART	number	SNP18AGHS_	phase	Production
	name			
	SNP18A HOSE CLAMP			
	material			
	NYLON 6/6 13% GLASS FILLED; HEAT STABILIZED			

DRAWING	format	version	C	CAD	SW 2006	scale	5:1
	computer file name	CP05-049-001CST_03					previous drawing number
	drawn	K.A.C.	checked	K.A.C.	approved		
	date	08/03/2004	date	04/20/2006			
	type	Customer	sheet 1 of 1				
number	CP05-049-001CST						