

111-01572

HellermannTyton



Article Number: 111-01572

Description: Heavy-Duty Cable Tie, 21" Long, UL Rated, 175lb Tensile Strength, POM, Black, 25/pkg

Base Data		
	Local Order Number	111-01572
	Type	T150M
	Color	Black (BK)
	Features and benefits	• Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
	Quantity Per	bag
	Product Description	HellermannTyton Heavy-Duty Cable Ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
	Short Description	Heavy-Duty Cable Tie, 21" Long, UL Rated, 175lb Tensile Strength, POM, Black, 25/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	175.0lbs
	Minimum Tensile Strength (Metric)	780.0N
	Length L (Imperial)	21.0"
	Length L (Metric)	525mm
	Fixation Method	None
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.35"
	Width W (Metric)	8.9mm
	Bundle Diameter Min. (Imperial)	0.32"
	Bundle Diameter Min. (Metric)	8.0mm
	Bundle Diameter Max. (Imperial)	5.9"

111-01572



Product Dimensions	Bundle Diameter Max. (Metric)	150.0mm
	Thickness T (Metric)	1.9mm
Material and Specifications		
	Material	Polyacetal (POM)
	Material Shortcut	POM
	Flammability	UL 94 HB
	Halogenfree	Yes
	Operating Temperature	-40°F to +194°F (-40°C to +90°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	25
	Package Quantity (Metric)	25
	Customs Number(Schedule B)	3926909987