

112-52103

HellermannTyton

Article Number: 112-52103

Description: Clamp Tie, 8" Long, 60lb Tensile Strength, PA66, Blue, 1000/pkg



Base Data		
	Local Order Number	CTT60R6M4
	Type	CTT60R
	Color	Blue (BU)
	Features and benefits	• Head design contains clamping rails to provide full circumferential compression around bundles. • Bent tail allows for quick insertion into head.
	Quantity Per	bag
	Product Description	The 360 Degree compression ties were designed with underside clamping rails to allow for optimal surface contact and complete circumferential compression around the bundle. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
	Short Description	Clamp Tie, 8" Long, 60lb Tensile Strength, PA66, Blue, 1000/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	60.0lbs
	Minimum Tensile Strength (Metric)	265.0N
	Length L (Imperial)	8.0"
	Length L (Metric)	205.0mm
	Fixation Method	None
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.19"
	Width W (Metric)	4.7mm
	Bundle Diameter Min. (Imperial)	0.06"
	Bundle Diameter Min. (Metric)	1.5mm
	Bundle Diameter Max. (Imperial)	1.8"

112-52103

HellermannTyton

Product Dimensions	Bundle Diameter Max. (Metric)	45.0mm
	Thickness T (Metric)	1.2mm
Material and Specifications		
	Material	Polyamide 6.6 (PA66)
	Material Shortcut	PA66
	Flammability	UL 94 V2
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
	Certification/Specification	UL
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1000
	Package Quantity (Metric)	1000
	Customs Number(Schedule B)	3926909987