

157-00050

# HellermannTyton

Article Number: 157-00050



Description: 1-Piece Cable Tie/Fir Tree Mount With Disc, 6.5"L, 6.5–7.2 mm Mounting Hole, PA66HS, Black, 500/pkg

Base Data		
	Local Order Number	157-00050
	Type	T50SOSFT6LGU
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Outside serrations on the tie strap minimize potential damage to the bundle.</li> <li>• Low profile tie head design allows the tie to follow the contour of the bundle and center the bundle directly over the mounting hole.</li> <li>• Tapered and bent tie strap tail makes it easier to locate and install the strap during the installation process.</li> <li>• Grips on both sides of the tie strap tail allow for a stronger hold when tensioning the strap.</li> </ul>
	Quantity Per	bag
	Product Description	Fir Tree Mounts offers a simple and easy to use method of bundling and mounting cables. The design of the fir tree ensures a secure and robust fit into panels with a round mounting hole between 6.5-7.2mm and a thickness between 0.6mm-8.5mm. The 'disc' on the top of the fir tree covers the hole and minimizes the ingress of water and dirt. This can be applied by hand and tensioned with one of HellermannTyton's manual or pneumatic hand tools.
	Short Description	1-Piece Cable Tie/Fir Tree Mount With Disc, 6.5"L, 6.5–7.2 mm Mounting Hole, PA66HS, Black, 500/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	225N
	Length L (Imperial)	6.5"
	Length L (Metric)	169.0mm
	Fixation Method	Fir Tree
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Outside Serrated
	Width W (Imperial)	0.2"
	Width W (Metric)	5.1mm

157-00050



Product Dimensions	Bundle Diameter Max. (Imperial)	1.4"
	Bundle Diameter Max. (Metric)	35.0mm
	Panel Thickness Max. (Imperial)	0.33"
	Panel Thickness Max. (Metric)	8.5mm
	Panel Thickness Min. (Imperial)	0.02"
	Panel Thickness Min. (Metric)	0.6mm
	Mounting Hole Diameter D (Imperial)	0.255 - 0.283"
	Mounting Hole Diameter D (Metric)	6.5 - 7.2 mm
	Mounting Hole Diameter D Min. (Imperial)	0.283"
	Mounting Hole Diameter D Max. (Imperial)	0.255"
Material and Specifications		
	Material	Polyamide 6.6 heat stabilized (PA66HS)
	Material Shortcut	PA66HS
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500
	Customs Number(Schedule B)	3926909987