

157-00109

HellermannTyton



Article Number: 157-00109

Description: Fir Tree Mount Cable Tie, 6.3" Long, 6.3–7 mm Mounting Hole, 50lb, PA66HS, Yellow, 1000/pkg

Base Data		
	Local Order Number	157-00109
	Type	T50SOSFT6LG-E
	Color	Yellow (YE)
	Features and benefits	<ul style="list-style-type: none"> • One piece cable tie and fixing offers a simple and easy to use method of bundling and fixing cables. • The design of the fir tree ensures a positive and secure fixing into panels with thicknesses from 0.8mm to 7.0mm or threaded blind holes. • Disc on the top of the fir tree covers the hole and minimizes the ingress of water and dirt.
	Quantity Per	bag
	Product Description	Fir Tree Mounts offers a simple and easy to use method of bundling and mounting cables. The design of the fir tree ensures a secure and robust fit into panels with a round mounting hole between thicknesses between .03" - .28". The 'disc' on the top of the fir tree covers the hole and minimizes the ingress of water and dirt. The outside serrated tie can be applied by hand and tensioned with one of HellermannTyton's manual or pneumatic hand tools.
	Short Description	Fir Tree Mount Cable Tie, 6.3" Long, 6.3–7 mm Mounting Hole, 50lb, PA66HS, Yellow, 1000/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	180N
	Length L (Imperial)	6.3"
	Length L (Metric)	165.0mm
	Fixation Method	Fir Tree
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Outside Serrated
	Width W (Imperial)	0.18"
	Width W (Metric)	4.6mm
	Bundle Diameter Min. (Imperial)	0.04"

157-00109



Product Dimensions	Bundle Diameter Min. (Metric)	1.0mm
	Bundle Diameter Max. (Imperial)	1.4"
	Bundle Diameter Max. (Metric)	35.0mm
	Disc Diameter (Imperial)	0.63"
	Disc Diameter (Metric)	16.0mm
	Panel Thickness Max. (Imperial)	0.28"
	Panel Thickness Max. (Metric)	7.00mm
	Panel Thickness Min. (Imperial)	0.03"
	Panel Thickness Min. (Metric)	0.70mm
	Mounting Hole Diameter D (Imperial)	0.25 - 0.28"
	Mounting Hole Diameter D (Metric)	6.3 - 7.0 mm
	Thickness T (Imperial)	0.05"
	Thickness T (Metric)	1.3mm
Material and Specifications		
	Material	Polyamide 6.6 heat stabilized (PA66HS)
	Material Shortcut	PA66HS
	Flammability	UL 94 V2
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1000
	Package Quantity (Metric)	1000
	Customs Number(Schedule B)	3926909987
	Weight (Metric)	1.50kg