

170-03188



Article Number: 170-03188

Description: Braided Sleeving, Split Wrap, 2" Dia, PET, White, 150 ft/bulk reel



Base Data		
	Local Order Number	170-03188
	Type	BSPSW2010LB
	Color	White (WH)
	Features and benefits	<ul style="list-style-type: none">• Split wrap design installs quickly, saving assembly time and future accessibility without disassembly.• Unique construction retains shape and rigidity throughout unrolling.• Easy open design allows quick assembly, future access, and ability to apply protective sleeving post assembly or post installation situations.
	Quantity Per	box
	Product Description	A lateral split, semi-rigid and flame retardant braided sleeving configuration used when ease of installation and repeat access to wire bundle is required. The lateral split allows the sleeving to open and accommodate a variety of bundling requirements. The 25% edge overlap rolls back over connectors and splices without exposing the bundled wires.
	Short Description	Braided Sleeving, Split Wrap, 2" Dia, PET, White, 150 ft/bulk reel
Product Dimensions		
	Length L (Imperial)	150.0ft
	Reel Length (imperial)	150.0ft
Material and Specifications		
	Material	Polyester (PET)
	Material Shortcut	PET
	Flammability	UL 94 V0
	Operating Temperature	-94°F to +248°F (-70°C to +125°C)
	ROHS Compliant	Yes
	UL Recognized (US and Canada)	Yes

170-03188



Logistic and Packaging		
	Package Quantity (Imperial)	150ft
	Package Quantity (Metric)	45.72m