

190-00079

HellermannTyton



Article Number: 190-00079

Description: Snapper Hose Clamp, .74"–.84" Bundle Diameter, POM, White, 1000/pkg

Base Data		
	Local Order Number	SNP1610M4
	Type	SNP16
	Color	White (WH)
	Features and benefits	<ul style="list-style-type: none"> • Installation and removal can be five times faster than conventional clamps • Heat stabilized material is suitable for high temperature applications. • Completely reusable • Will not rust or corrode • Safety engineered. • No protruding band or cluster. • Can be installed with hose in place • One-hand installation for tight places.
	Quantity Per	bag
	Product Description	<p>Snapper Hose Clamps are lightweight and corrosion-resistant. Manufactured from high-performance thermoplastic materials selected to work well in a variety of diverse environments.</p> <p>A quick ratchet closure provides for reduced assembly line time and allows for application after connection of the hose. Release is achieved by initiating opposed lateral movement of the ratchet ends.</p> <p>Heat stabilized materials are available for high-temperature, motor, and under-hood applications. Snappers are also stable in a wide variety of chemicals including salts, bases, alcohols, ethers, detergents, gasoline, lubricating oils, and greases.</p> <p>The Snapper is available in 32 standard sizes ranging from 1/4" to 4-1/2" ID. Snappers are manufactured in white polyacetal and black polyamide 6.6 glass filled impact modified heat stabilized material. Custom designed and different colored or shaped Snappers are available based upon applications and volume requirements.</p>
	Short Description	Snapper Hose Clamp, .74"–.84" Bundle Diameter, POM, White, 1000/pkg
Product Dimensions		
	Fixation Method	Plug-in mounting
	Variant	Closed
	Width W2 (Imperial)	0.23"
	Width W2 (Metric)	5.84mm

190-00079

HellermannTyton

Product Dimensions	Diameter Min. (Imperial)	0.743"
	Diameter Min. (Metric)	18.87mm
	Diameter Max. (Imperial)	0.837"
	Diameter Max. (Metric)	21.26mm
	Wall Thickness WT (Imperial)	.067"
	Wall Thickness WT (Metric)	1.7mm
Material and Specifications		
	Material	Polyacetal (POM)
	Material Shortcut	POM
	Flammability	UL 94 HB
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1000
	Package Quantity (Metric)	1000
	Customs Number(Schedule B)	3926909987