

190-00119

HellermannTyton

Article Number: 190-00119



Description: Snapper Hose Clamp, 1.0"–1.17" Bundle Diameter, PA66GF13, Black, 500/pkg

Base Data		
	Local Order Number	SNP24GHS0H4
	Type	SNP24
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Designed for quick, ratcheted installation and can be released and reused. • Heat stabilized material is suitable for high temperature applications.
	Quantity Per	bag
	Product Description	HellermannTyton snapper hose clamps are designed to provide a quick, ratcheted closure reducing installation time. The design also allows the clamp to be easily removed and re-applied when necessary. Snappers are made of high performing materials providing stability in a variety of diverse environments. Available in 32 standard sizes.
	Short Description	Snapper Hose Clamp, 1.0"–1.17" Bundle Diameter, PA66GF13, Black, 500/pkg
Product Dimensions		
	Fixation Method	Plug-in mounting
	Variant	Closed
	Width W2 (Imperial)	0.291"
	Width W2 (Metric)	7.39mm
	Diameter Min. (Imperial)	1.016"
	Diameter Min. (Metric)	25.81mm
	Diameter Max. (Imperial)	1.169"
	Diameter Max. (Metric)	29.69mm
	Wall Thickness WT (Imperial)	.1"
	Wall Thickness WT (Metric)	2.54mm
Material and Specifications		
	Material	Polyamide 6.6 glass filled impact modified heat stabilized (PA66GF13%)
	Material Shortcut	PA66GF13

190-00119



Material and Specifications	Flammability	UL 94 HB
	Operating Temperature	-40°F to +221°F (-40°C to +105°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	500
	Package Quantity (Metric)	500
	Customs Number(Schedule B)	3926909987