

401-06036

# HellermannTyton

Article Number: 401-06036

Description: Heatshrink Moulded Shapes, 100 series Bottle with Rib - MIL, 106-4-G, PO-X, BK, 1/bag



|                    |                       |                                                                                                                                                                                                                           |
|--------------------|-----------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Base Data          |                       |                                                                                                                                                                                                                           |
|                    | Local Order Number    | 401-06036                                                                                                                                                                                                                 |
|                    | Type                  | 106-4-G                                                                                                                                                                                                                   |
|                    | Color                 | Black (BK)                                                                                                                                                                                                                |
|                    | Features and benefits | <ul style="list-style-type: none"> <li>• Uses a circular grooved adaptor for strain relief.</li> <li>• Combine with complementary adhesives for environmental sealing.</li> </ul>                                         |
|                    | Quantity Per          | bag                                                                                                                                                                                                                       |
|                    | Product Description   | Heatshrink 100 series, with rib, is used in conjunction with a circular grooved adaptor providing strain relief and environmental sealing when used in conjunction with one of HellermannTyton's complementary adhesives. |
|                    | Short Description     | Heatshrink Moulded Shapes, 100 series Bottle with Rib -MIL, 106-4-G, PO-X, BK, 1/bag                                                                                                                                      |
| Product Dimensions |                       |                                                                                                                                                                                                                           |
|                    | HW ± 20 % b           | 1.8mm                                                                                                                                                                                                                     |
|                    | HW ± 20% b (imperial) | .07"                                                                                                                                                                                                                      |
|                    | JW ± 20 % b           | 1.8mm                                                                                                                                                                                                                     |
|                    | JW ± 20% b (imperial) | .07"                                                                                                                                                                                                                      |
|                    | H max b (imperial)    | .55"                                                                                                                                                                                                                      |
|                    | H min a (imperial)    | 1.21"                                                                                                                                                                                                                     |
|                    | J min. a (imperial)   | 1.21"                                                                                                                                                                                                                     |
|                    | P ±10% b (imperial)   | 2.16"                                                                                                                                                                                                                     |
|                    | R max.b (imperial)    | 1.03"                                                                                                                                                                                                                     |
|                    | S nom (imperial)      | .4"                                                                                                                                                                                                                       |
|                    | T ± 20% b (imperial)  | .04"                                                                                                                                                                                                                      |
|                    | Flexibility           | Semi Rigid                                                                                                                                                                                                                |
|                    | H max b               | 14.2mm                                                                                                                                                                                                                    |
|                    | H min a               | 31mm                                                                                                                                                                                                                      |
|                    | J max. b              | 6.6mm                                                                                                                                                                                                                     |

401-06036

**HellermannTyton**

|                             |                              |                                    |
|-----------------------------|------------------------------|------------------------------------|
| Product Dimensions          | J min. a                     | 31mm                               |
|                             | P ±10 % b                    | 55.4mm                             |
|                             | R max.b                      | 26.5mm                             |
|                             | S nom (metric)               | 10.2mm                             |
| Material and Specifications |                              |                                    |
|                             | Material                     | Polyolefin, cross-linked (PO-X)    |
|                             | Material Shortcut            | PO-X                               |
|                             | Dielectric Strength (Metric) | 14 kV/mm according to ASTM D2671   |
|                             | Flammability                 | ASTM D635                          |
|                             | Shrink Temperature           | +275 °F (+135 °C)                  |
|                             | Operating Temperature        | -103°F to +302°F (-75°C to +150°C) |
|                             | ROHS Compliant               | Yes                                |
| Logistic and Packaging      |                              |                                    |
|                             | Package Quantity (Imperial)  | 1                                  |
|                             | Package Quantity (Metric)    | 1                                  |