



## SAFETY DATA SHEET

ADESCO PIPE SEAL 50ML

Page: 1

Compilation date: 05/07/2017

Revision No: 6

### Section 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

**Product name:** ADESCO PIPE SEAL 50ML

**Product code:** ASADAN1M500908

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

**Use of substance / mixture:** PC1: Adhesives, sealants.

#### 1.3. Details of the supplier of the safety data sheet

**Company name:** Anixter

3 Edmund Road

Sheffield

S2 4EB

England

**Tel:** +44 (0)1142 709338

**Fax:** +44 (0)1142 709358

**Email:** [gregg.walker@anixter.com](mailto:gregg.walker@anixter.com)

#### 1.4. Emergency telephone number

**Emergency tel:** +44 (0)1142 709338

(office hours only)

### Section 2: Hazards identification

#### 2.1. Classification of the substance or mixture

**Classification under CLP:** Aquatic Chronic 2: H411; Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317; -: EUH208

**Most important adverse effects:** Contains 1-acetyl-2-phenylhydrazine. May produce an allergic reaction. Causes skin irritation. May cause an allergic skin reaction. Causes serious eye irritation. Toxic to aquatic life with long lasting effects.

#### 2.2. Label elements

**Label elements:**

**Hazard statements:** EUH208: Contains 1-acetyl-2-phenylhydrazine. May produce an allergic reaction.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H411: Toxic to aquatic life with long lasting effects.

**Hazard pictograms:** GHS07: Exclamation mark

GHS09: Environmental

[cont...]

# SAFETY DATA SHEET

ADESCO PIPE SEAL 50ML

Page: 2



**Signal words:** Warning

**Precautionary statements:** P264: Wash contaminated skin thoroughly after handling.  
P273: Avoid release to the environment.  
P280: Wear protective gloves/protective clothing/eye protection/face protection.  
P302+352: IF ON SKIN: Wash with plenty of water/.  
P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P321: Specific treatment (see information on this label).  
P332+313: If skin irritation occurs: Get medical advice/attention.  
P337+313: If eye irritation persists: Get medical advice/attention.  
P501: Dispose of contents/container to comply with Local, National and International regulations.

## 2.3. Other hazards

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

##### POLYGLYCOL DIMETHACRYLATE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
203-652-6	109-16-0	-	Skin Sens. 1: H317	10-30%

##### BIS(ISOPROPYL)NAPHTHALENE

254-052-6	38640-62-9	-	Aquatic Acute 1: H400; Aquatic Chronic 2: H411	10-30%
-----------	------------	---	--	--------

##### HYDROXYALKYL METHACRYLATE

248-666-3	27813-02-1	-	STOT SE 3: H335; Eye Irrit. 2: H319; Skin Sens. 1: H317	1-10%
-----------	------------	---	---	-------

##### CUMENE HYDROPEROXIDE

201-254-7	80-15-9	-	Org. Perox. EF: H242; Acute Tox. 3: H331; Acute Tox. 4: H312; Acute Tox. 4: H302; STOT RE 2: H373; Skin Corr. 1B: H314	1-10%
-----------	---------	---	--	-------

[cont...]

## SAFETY DATA SHEET

ADESCO PIPE SEAL 50ML

Page: 3

### ACRYLIC ACID

201-177-9	79-10-7	-	Flam. Liq. 3: H226; Acute Tox. 4: H332; Acute Tox. 4: H312; Acute Tox. 4: H302; Skin Corr. 1A: H314; Aquatic Acute 1: H400	<1%
-----------	---------	---	---	-----

### 1-ACETYL-2-PHENYLHYDRAZINE

204-055-3	114-83-0	-	Acute Tox. 3: H301+311; Skin Irrit. 2: H315; STOT SE 3: H335; Aquatic Chronic 1: H410; Eye Irrit. 2: H319; Skin Sens. 1B: H317	<1%
-----------	----------	---	---	-----

### N,N-DIMETHYL-P-TOLUIDINE

202-805-4	99-97-8	-	Acute Tox. 3: H331; Acute Tox. 3: H311; Acute Tox. 3: H301; STOT RE 2: H373; Aquatic Chronic 3: H412	<1%
-----------	---------	---	--	-----

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Wash immediately with plenty of soap and water. Consult a doctor.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

**Ingestion:** Wash out mouth with water. Do not induce vomiting. If conscious, give half a litre of water to drink immediately. Consult a doctor.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur. There may be vomiting.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

### 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate / special treatment:** Not applicable.

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes.

[cont...]

# SAFETY DATA SHEET

ADESCO PIPE SEAL 50ML

Page: 4

## 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details. If outside do not approach from downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Turn leaking containers leak-side up to prevent the escape of liquid.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

### 6.4. Reference to other sections

**Reference to other sections:** Refer to section 8 of SDS.

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Avoid the formation or spread of mists in the air.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in a cool, well ventilated area. Keep container tightly closed. The floor of the storage room must be impermeable to prevent the escape of liquids.

### 7.3. Specific end use(s)

**Specific end use(s):** No data available.

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Hazardous ingredients:**

ACRYLIC ACID

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
-------	------------	--------------	------------	--------------

[cont...]

# SAFETY DATA SHEET

ADESCO PIPE SEAL 50ML

Page: 5

UK	30 mg/m3	60 mg/m3	-	-
----	----------	----------	---	---

## DNEL/PNEC Values

**DNEL / PNEC** No data available.

## 8.2. Exposure controls

**Engineering measures:** Ensure there is sufficient ventilation of the area. The floor of the storage room must be impermeable to prevent the escape of liquids.

**Respiratory protection:** Self-contained breathing apparatus must be available in case of emergency.

**Hand protection:** Impermeable gloves.

**Eye protection:** Safety glasses. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Liquid

**Colour:** Pale yellow

**Odour:** Barely perceptible odour

**Evaporation rate:** No data available.

**Oxidising:** No data available.

**Solubility in water:** Slightly soluble

**Viscosity:** No data available.

**Boiling point/range°C:** >35

**Melting point/range°C:** No data available.

**Flammability limits %: lower:** No data available.

**upper:** No data available.

**Flash point°C:** >93

**Part.coeff. n-octanol/water:** No data available.

**Autoflammability°C:** No data available.

**Vapour pressure:** No data available.

**Relative density:** 1.1

**pH:** No data available.

**VOC g/l:** 48.6

### 9.2. Other information

**Other information:** No data available.

## Section 10: Stability and reactivity

### 10.1. Reactivity

**Reactivity:** Stable under recommended transport or storage conditions.

### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

[cont...]

# SAFETY DATA SHEET

ADESCO PIPE SEAL 50ML

Page: 6

## 10.4. Conditions to avoid

**Conditions to avoid:** Heat.

## 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong acids.

## 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

**Hazardous ingredients:**

#### CUMENE HYDROPEROXIDE

ORL	MUS	LDLO	5	gm/kg
ORL	RAT	LD50	382	mg/kg
SCU	RAT	LD50	382	mg/kg

#### ACRYLIC ACID

IPR	RAT	LD50	22	mg/kg
ORL	MUS	LD50	830	mg/kg
ORL	RAT	LD50	1250	mg/kg
SCU	MUS	LD50	1590	mg/kg

#### N,N-DIMETHYL-P-TOLUIDINE

IPR	MUS	LD50	212	mg/kg
-----	-----	------	-----	-------

**Relevant hazards for product:**

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
Respiratory/skin sensitisation	DRM	Hazardous: calculated

### Symptoms / routes of exposure

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. The eyes may water profusely.

**Ingestion:** There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur. There may be vomiting.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

[cont...]

# SAFETY DATA SHEET

ADESCO PIPE SEAL 50ML

Page: 7

## Section 12: Ecological information

### 12.1. Toxicity

**Ecotoxicity values:** No data available.

### 12.2. Persistence and degradability

**Persistence and degradability:** Not biodegradable.

### 12.3. Bioaccumulative potential

**Bioaccumulative potential:** Bioaccumulation potential.

### 12.4. Mobility in soil

**Mobility:** Readily absorbed into soil.

### 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

### 12.6. Other adverse effects

**Other adverse effects:** Toxic to aquatic organisms. Toxic to soil organisms.

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

### 14.1. UN number

**UN number:** UN3082

### 14.2. UN proper shipping name

**Shipping name:** ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.  
(BIS(ISOPROPYL)NAPHTHALENE)

### 14.3. Transport hazard class(es)

**Transport class:** 9

### 14.4. Packing group

**Packing group:** III

### 14.5. Environmental hazards

**Environmentally hazardous:** Yes

**Marine pollutant:** No

[cont...]

# SAFETY DATA SHEET

ADESCO PIPE SEAL 50ML

Page: 8

## 14.6. Special precautions for user

**Special precautions:** No special precautions.

**Tunnel code:** E

**Transport category:** 3

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

### 15.2. Chemical Safety Assessment

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

\* indicates text in the SDS which has changed since the last revision.

**Phrases used in s.2 and s.3:** EUH208: Contains <name of sensitising substance>. May produce an allergic reaction.

H226: Flammable liquid and vapour.

H242: Heating may cause a fire.

H301: Toxic if swallowed.

H301+311: Toxic if swallowed or in contact with skin.

H302: Harmful if swallowed.

H311: Toxic in contact with skin.

H312: Harmful in contact with skin.

H314: Causes severe skin burns and eye damage.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H331: Toxic if inhaled.

H332: Harmful if inhaled.

H335: May cause respiratory irritation.

H373: May cause damage to organs <or state all organs affected, if known> through prolonged or repeated exposure <state route of exposure if it is conclusively proven that no other routes of exposure cause the hazard>.

H400: Very toxic to aquatic life.

H410: Very toxic to aquatic life with long lasting effects.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.