

553-50251

HellermannTyton



Article Number: 553-50251

Description: Heat Shrink Labels, .38" (9.52mm), Single Sided, 2 Slit, PO-X, White, 750/box

Base Data		
	Local Order Number	553-50251
	Type	HST9-3WH-2S
	Color	White (WH)
	Features and benefits	<ul style="list-style-type: none"> • Slide Slit and optional center slits for easy wire insertion. • Smooth surface for clean and legible printing. • Supplied on a ladder style carrier so that markers can be kitted after printing. • A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.
	Quantity Per	box
	Product Description	HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.
	Short Description	Heat Shrink Labels, .38" (9.52mm), Single Sided, 2 Slit, PO-X, White, 750/box
Product Dimensions		
	Length L (Imperial)	0.597"
	Printable (Yes/No)	Yes
	Variant	Thin-Wall
	Height H (Imperial)	.60"
	Height H (Metric)	15.16mm
	Diameter Max. (Imperial)	0.375"
	Outside Diameter Max. (Imperial)	0.375"
	Outside Diameter Max. (Metric)	9.52mm
	Wall Thickness WT (Imperial)	0.033"
	Wall Thickness WT (Metric)	0.80mm
	Flexibility	Flexible
	Print Method	Thermal transfer
	Recovered Diameter d (metric)	3.0mm

553-50251

HellermannTyton

Product Dimensions	Recovered Diameter d (imperial)	0.122"
	Supplied Diameter D (metric)	9.0mm
	Supplied Diameter D (imperial)	0.354"
	Thickness T (Metric)	3.0µm
	Width of Liner WL (imperial)	3.0"
	Width of Liner WL (metric)	76.2mm
Material and Specifications		
	Material	Polyolefin, cross-linked (PO-X)
	Material Shortcut	PO-X
	US MILSPEC	MIL-STD-202G Method 215K
	Dielectric Strength (Metric)	19.7 kV min.
	Flammability	UL 224 VW-1
	Shrink Temperature	+194 °F (+90 °C)
	Operating Temperature	-67°F to +275°F (-55°C to +135°C)
	ROHS Compliant	Yes
	Certification/Specification	SAE - AMS - DTL-23053/5 Class 1 and 3
Logistic and Packaging		
	Package Quantity (Imperial)	750
	Package Quantity (Metric)	750Pieces