



SAFETY DATA SHEET
ADESCO AD100 CYANO 20G

Page: 1

Compilation date: 05/07/2017

Revision No: 4

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: ADESCO AD100 CYANO 20G

Product code: ASADCY1G200005

Synonyms: SUPER GLUE

ETHYL-2-CYANOACRYLATE ESTER

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Cyanoacrylate adhesive

1.3. Details of the supplier of the safety data sheet

Company name: Anixter

3 Edmund Road

Sheffield

S2 4EB

England

Tel: +44 (0)1142 709338

Fax: +44 (0)1142 709358

Email: gregg.walker@anixter.com

1.4. Emergency telephone number

Emergency tel: +44 (0)1142 709338

(office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: STOT SE 3: H335; Eye Irrit. 2: H319; Skin Irrit. 2: H315; -: EUH202

Most important adverse effects: Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation. Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

2.2. Label elements

Label elements:

Hazard statements: H315: Causes skin irritation.

H319: Causes serious eye irritation.

H335: May cause respiratory irritation.

EUH202: Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

Hazard pictograms: GHS07: Exclamation mark

[cont...]

SAFETY DATA SHEET

ADESCO AD100 CYANO 20G

Page: 2



Signal words: Warning

Precautionary statements: P261: Avoid breathing vapours.
P264: Wash hands thoroughly after handling.
P271: Use only outdoors or in a well-ventilated area.
P280: Wear protective gloves/protective clothing/eye protection/face protection.
P302+352: IF ON SKIN: Wash with plenty of water/.
P304+340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P312: Call a if you feel unwell.
P332+313: If skin irritation occurs: Get medical advice/attention.
P337+313: If eye irritation persists: Get medical advice/attention.
P501: Dispose of contents/container to comply with Local, National and International regulations.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

ETHYL-2-CYANOACRYLATE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
230-391-5	7085-85-0	-	Eye Irrit. 2: H319; STOT SE 3: H335; Skin Irrit. 2: H315	70-90%

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Transfer to hospital for specialist examination.

Ingestion: Wash out mouth with water.

Inhalation: Not applicable.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be pain and redness. The eyes may water profusely. There may be severe pain. The vision may become blurred. May cause permanent damage.

[cont...]

SAFETY DATA SHEET

ADESCO AD100 CYANO 20G

Page: 3

Ingestion: There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Mark out the contaminated area with signs and prevent access to unauthorised personnel. Do not attempt to take action without suitable protective clothing - see section 8 of SDS. Turn leaking containers leak-side up to prevent the escape of liquid.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Avoid the formation or spread of mists in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Must only be kept in original packaging.

[cont...]

SAFETY DATA SHEET

ADESCO AD100 CYANO 20G

Page: 4

7.3. Specific end use(s)

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

ETHYL-2-CYANOACRYLATE

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	-	1.5 mg/m ³	-	-

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Protective gloves.

Eye protection: Tightly fitting safety goggles. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Colourless

Odour: Sharp characteristic odour.

Solubility in water: Insoluble

Also soluble in: Acetone. (Completely soluble)

Boiling point/range°C: 150

Flash point°C: 60 - 93

Vapour pressure: 0.293 mmHg

Relative density: 1.04

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

[cont...]

SAFETY DATA SHEET

ADESCO AD100 CYANO 20G

Page: 5

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Toxicity values:

Route	Species	Test	Value	Units
DERMAL	RBT	LD50	>2000	mg/kg
ORAL	RAT	LD50	>5000	mg/kg

Hazardous ingredients:

ETHYL-2-CYANOACRYLATE

ORL	RAT	LD50	>5	ml/kg
-----	-----	------	----	-------

Relevant hazards for product:

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
STOT-single exposure	INH	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be pain and redness. The eyes may water profusely. There may be severe pain. The vision may become blurred. May cause permanent damage.

Ingestion: There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

Section 12: Ecological information

[cont...]

SAFETY DATA SHEET

ADESCO AD100 CYANO 20G

Page: 6

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: EUH202: Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the

[cont...]

SAFETY DATA SHEET
ADESCO AD100 CYANO 20G

Page: 7

reach of children.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H335: May cause respiratory irritation.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.