

558-00216



Article Number: 558-00216

Description: SwiftMark Self-Laminating Label, 2.0" x .5" x 1.0", VL, White, 4500/roll



Base Data		
	Local Order Number	558-00216
	Type	TAG20-47W508SM
	Color	Brown (BN)
	Features and benefits	<ul style="list-style-type: none"> • HellermannTyton SwiftMark Self-Laminating Labels come on rolls for convenient loading and printing. • Labels are conformable so that they can bend around small gauge wires and tight bends without coming loose over time. • Labels are UL recognized for indoor and outdoor use to expand application options. • HellermannTyton SwiftMark Self-Laminating labels are designed for high speed printing and dispensing to work flawlessly in the SwiftMark applicator and printer.
	Quantity Per	reel
	Product Description	HellermannTyton's self-laminating labels are designed for use in the SwiftMark automatic label applicator and printer. Manufactured in a conformable frosty clear vinyl with good contrast clarity, they are designed with a clear overlap to protect the printed text. The labels come 1 across on a spindle that fits into the applicator. Labels are designed with a special adhesive that bonds quickly to wire and cable using a custom high speed dispensing liner. The printed labels can be used on wires as small as .06" (1.52mm) in diameter and as large as .75" (19mm) in diameter. A UL recognized mark for indoor and outdoor use can be achieved using the TT100 series ribbon (part no. 556-00165). SwiftMark vinyl label meet all the requirements of UL969 - STANDARD FOR MARKING AND LABELING SYSTEMS edition -4. Labels UL recognized under UL file number MH18396. The SwiftMark can accept labels widths that range from .5" (12.7mm) to 2.0" (50.8mm).
	Technical Description	SwiftMark Self-Laminating Label, 2.0" X .5" X 1.0", White
	Short Description	SwiftMark Self-Laminating Label, 2.0" x .5" x 1.0", VL, White, 4500/roll
Product Dimensions		
	Variant	Roller form
	Width W (Imperial)	2.0"
	Width W (Metric)	50.8mm
	Height H (Imperial)	.50"
	Height H (Metric)	12.70mm
	Height H2 (Imperial)	1.0"
	Height H2 (Metric)	25.40mm

558-00216



Product Dimensions	Bundle Diameter Min. (Imperial)	0.1"
	Bundle Diameter Min. (Metric)	2.6mm
	Bundle Diameter Max. (Imperial)	0.2"
	Bundle Diameter Max. (Metric)	5.3mm
	Outside Diameter Min. (Imperial)	0.078"
	Outside Diameter Min. (Metric)	2.0mm
	Outside Diameter Max. (Imperial)	0.18"
	Outside Diameter Max. (Metric)	4.7mm
	Horizontal Repeat HR (metric)	25.40mm
	Horizontal Repeat HR (imperial)	2.0"
	Print Method	Thermal transfer
	Thickness T (Metric)	25µm
	Vertical Repeat VR (imperial)	1.25"
	Vertical Repeat VR (metric)	31.75mm
	Width of Liner WL (imperial)	2.125"
	Width of Liner WL (metric)	53.97mm
Material and Specifications		
	Material	Type 100, Vinyl (PVC), white (WH), self laminating
	Material Shortcut	100B
	Adhesive	Acrylic
	Adhesive Operating Temperature	-40°F to +194°F (-40°C to +90°C)
	Minimum Application Temperature	from +50°F (from +10°C)
	Operating Temperature	-51°F to +200°F (-46°C to +93°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	4500
	Package Quantity (Metric)	4500
	Customs Number(Schedule B)	3919102055
	Labels per Row	1
	Weight (imperial)	4.5
	Weight (Metric)	2.04kg