



**SAFETY DATA SHEET**  
ADESCO AD150 CYANO 50G

Page: 1

Compilation date: 05/07/2017

Revision No: 4

**Section 1: Identification of the substance/mixture and of the company/undertaking**

**1.1. Product identifier**

**Product name:** ADESCO AD150 CYANO 50G

**Product code:** ASADCY1G500005

**Synonyms:** SUPER GLUE

ETHYL-2-CYANOACRYLATE ESTER

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

**Use of substance / mixture:** Cyanoacrylate adhesive

**1.3. Details of the supplier of the safety data sheet**

**Company name:** Anixter

3 Edmund Road

Sheffield

S2 4EB

England

**Tel:** +44 (0)1142 709338

**Fax:** +44 (0)1142 709358

**Email:** [gregg.walker@anixter.com](mailto:gregg.walker@anixter.com)

**1.4. Emergency telephone number**

**Emergency tel:** +44 (0)1142 709338

(office hours only)

**Section 2: Hazards identification**

**2.1. Classification of the substance or mixture**

**Classification under CLP:** STOT SE 3: H335; Eye Irrit. 2: H319; Skin Irrit. 2: H315; -: EUH202

**Most important adverse effects:** Causes skin irritation. Causes serious eye irritation. May cause respiratory irritation. Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

**2.2. Label elements**

**Label elements:**

**Hazard statements:** H315: Causes skin irritation.

H319: Causes serious eye irritation.

H335: May cause respiratory irritation.

EUH202: Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

**Hazard pictograms:** GHS07: Exclamation mark

[cont...]

# SAFETY DATA SHEET

ADESCO AD150 CYANO 50G

Page: 2



**Signal words:** Warning

**Precautionary statements:** P261: Avoid breathing vapours.  
P264: Wash hands thoroughly after handling.  
P271: Use only outdoors or in a well-ventilated area.  
P280: Wear protective gloves/protective clothing/eye protection/face protection.  
P302+352: IF ON SKIN: Wash with plenty of water/.  
P304+340: IF INHALED: Remove person to fresh air and keep comfortable for breathing.  
P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P312: Call a if you feel unwell.  
P332+313: If skin irritation occurs: Get medical advice/attention.  
P337+313: If eye irritation persists: Get medical advice/attention.  
P501: Dispose of contents/container to comply with Local, National and International regulations.

## 2.3. Other hazards

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

ETHYL-2-CYANOACRYLATE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
230-391-5	7085-85-0	-	Eye Irrit. 2: H319; STOT SE 3: H335; Skin Irrit. 2: H315	70-90%

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Wash immediately with plenty of soap and water.

**Eye contact:** Bathe the eye with running water for 15 minutes. Transfer to hospital for specialist examination.

**Ingestion:** Wash out mouth with water.

**Inhalation:** Not applicable.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be pain and redness. The eyes may water profusely. There may be severe pain. The vision may become blurred. May cause permanent damage.

[cont...]

# SAFETY DATA SHEET

## ADESCO AD150 CYANO 50G

Page: 3

**Ingestion:** There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

### 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate / special treatment:** Eye bathing equipment should be available on the premises.

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** In combustion emits toxic fumes.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Mark out the contaminated area with signs and prevent access to unauthorised personnel. Do not attempt to take action without suitable protective clothing - see section 8 of SDS. Turn leaking containers leak-side up to prevent the escape of liquid.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

### 6.4. Reference to other sections

**Reference to other sections:** Refer to section 8 of SDS.

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Avoid the formation or spread of mists in the air.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in a cool, well ventilated area. Keep container tightly closed.

**Suitable packaging:** Must only be kept in original packaging.

[cont...]

# SAFETY DATA SHEET

ADESCO AD150 CYANO 50G

Page: 4

## 7.3. Specific end use(s)

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Hazardous ingredients:**

**ETHYL-2-CYANOACRYLATE**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	-	1.5 mg/m <sup>3</sup>	-	-

### DNEL/PNEC Values

**DNEL / PNEC** No data available.

### 8.2. Exposure controls

**Engineering measures:** Ensure there is sufficient ventilation of the area.

**Respiratory protection:** Self-contained breathing apparatus must be available in case of emergency.

**Hand protection:** Protective gloves.

**Eye protection:** Tightly fitting safety goggles. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Liquid

**Colour:** Colourless

**Odour:** Sharp characteristic odour.

**Solubility in water:** Insoluble

**Also soluble in:** Acetone. (Completely soluble)

**Boiling point/range°C:** 150

**Flash point°C:** 60 - 93

**Vapour pressure:** 0.293 mmHg

**Relative density:** 1.04

### 9.2. Other information

**Other information:** No data available.

## Section 10: Stability and reactivity

### 10.1. Reactivity

**Reactivity:** Stable under recommended transport or storage conditions.

### 10.2. Chemical stability

**Chemical stability:** Stable under normal conditions.

[cont...]

# SAFETY DATA SHEET

## ADESCO AD150 CYANO 50G

Page: 5

### 10.3. Possibility of hazardous reactions

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.  
Decomposition may occur on exposure to conditions or materials listed below.

### 10.4. Conditions to avoid

**Conditions to avoid:** Heat.

### 10.5. Incompatible materials

**Materials to avoid:** Strong oxidising agents. Strong acids.

### 10.6. Hazardous decomposition products

**Haz. decomp. products:** In combustion emits toxic fumes.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

#### Toxicity values:

Route	Species	Test	Value	Units
DERMAL	RBT	LD50	>2000	mg/kg
ORAL	RAT	LD50	>5000	mg/kg

#### Hazardous ingredients:

##### ETHYL-2-CYANOACRYLATE

ORL	RAT	LD50	>5	ml/kg
-----	-----	------	----	-------

#### Relevant hazards for product:

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
STOT-single exposure	INH	Hazardous: calculated

### Symptoms / routes of exposure

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be pain and redness. The eyes may water profusely. There may be severe pain. The vision may become blurred. May cause permanent damage.

**Ingestion:** There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur.

**Inhalation:** There may be irritation of the throat with a feeling of tightness in the chest.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

## Section 12: Ecological information

[cont...]

# SAFETY DATA SHEET

## ADESCO AD150 CYANO 50G

Page: 6

### 12.1. Toxicity

**Ecotoxicity values:** No data available.

### 12.2. Persistence and degradability

**Persistence and degradability:** Biodegradable.

### 12.3. Bioaccumulative potential

**Bioaccumulative potential:** No bioaccumulation potential.

### 12.4. Mobility in soil

**Mobility:** Readily absorbed into soil.

### 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

### 12.6. Other adverse effects

**Other adverse effects:** Negligible ecotoxicity.

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company.

**Disposal of packaging:** Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

**Transport class:** This product does not require a classification for transport.

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

**Specific regulations:** Not applicable.

### 15.2. Chemical Safety Assessment

**Chemical safety assessment:** A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

\* indicates text in the SDS which has changed since the last revision.

**Phrases used in s.2 and s.3:** EUH202: Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the

[cont...]

**SAFETY DATA SHEET**  
ADESCO AD150 CYANO 50G

**Page: 7**

reach of children.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H335: May cause respiratory irritation.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.