

596-00840

# HellermannTyton

Article Number: 596-00840



Description: Metal Solar Placard, Hand Writable, 2017 Code, AC Module, 4.0" x 2.0", AL, Black, 5/pkg

Base Data		
	Local Order Number	596-00840
	Type	AC2011M5
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Placards made with UV stable inks and materials tested to last up to 25 years, even in direct sun exposure.</li> <li>• Aggressive adhesive ensures strong bond, even on powder coated surfaces.</li> <li>• Meets or exceeds NEC &amp; IFC standards for printed text, character height, color and outdoor UV stability.</li> <li>• Optional Paint Shields provide additional protection for pre-printed and variable data placards.</li> </ul>
	Quantity Per	pack
	Product Description	Metal Solar Placards offer maximum durability for labeling photovoltaic equipment and components. A special printing process fuses UV stable inks to the placards for long-lasting results, tested to last up to 25 years—even in direct sunlight. Metal Solar Placards are designed to meet or exceed National Electrical Code (NEC) and the requirements of local Authorities Having Jurisdiction (AHJs), that may prefer a placard-style marking over thermal transfer printed labels.
	Technical Description	4" X 2" Silver Aluminum text on black background that reads as: "NOMINAL AC VOLTAGE;NOMINAL OPERATING AC FREQUENCY;MAXIMUM AC POWER;MAXIMUM AC CURRENT;MAXIMUM OVERCURRENT DEVICE RATING FOR AC MODULE PROTECTION." 10 per pack. Nameplate is also printable using a paint pen to add the variable voltage information on demand.
	Local Order Number 2	Cross Reference = Paint Shield: 596-00794
Product Dimensions	Short Description	Metal Solar Placard, Hand Writable, 2017 Code, AC Module, 4.0" x 2.0", AL, Black, 5/pkg
	Length L (Imperial)	4.0"
	Length L (Metric)	101.6mm
	Width W (Imperial)	4.0"
	Width W (Metric)	101.6mm
	Height H (Imperial)	2.0"
	Height H (Metric)	50.80mm

596-00840



Material and Specifications		
	Material	Anodized Aluminum (AA)
	Material Shortcut	AA
	Adhesive	Ultra High Bond Permanent Acrylic Adhesive
	Adhesive Operating Temperature	from +50°F (from +10°C)
	Halogenfree	Yes
	Operating Temperature	-40°F to +203°F (-40°C to +95°C)
	ROHS Compliant	Yes
	Certification/Specification	NEC2014
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	5
	Package Quantity (Metric)	5
	Customs Number(Schedule B)	7616995095