

596-00866

HellermannTyton

Article Number: 596-00866


 Description: Metal Solar Placard, Blank Plate For Engraving, 2.0" x 1.25", AL, Black, 5/pkg

Base Data	Local Order Number	596-00866
	Type	BLANK2X125
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Placards made with UV stable inks and materials tested to last up to 25 years, even in direct sun exposure. • Aggressive adhesive ensures strong bond, even on powder coated surfaces. • Meets or exceeds NEC & IFC standards for printed text, character height, color and outdoor UV stability. • Optional Paint Shields provide additional protection for pre-printed and variable data placards.
	Quantity Per	pieces
	Product Description	Metal Solar Placards offer maximum durability for labeling photovoltaic equipment and components. A special printing process fuses UV stable inks to the placards for long-lasting results, tested to last up to 25 years—even in direct sunlight. Metal Solar Placards are designed to meet or exceed National Electrical Code (NEC) and the requirements of local Authorities Having Jurisdiction (AHJs), that may prefer a placard-style marking over thermal transfer printed labels.
	Technical Description	2.0" X 1.25" Black surface for engraving custom metal placards. - 5 per pack.
	Short Description	Metal Solar Placard, Blank Plate For Engraving, 2.0" x 1.25", AL, Black, 5/pkg
	Product Dimensions	Length L (Imperial)
Length L (Metric)		50.8mm
Width W (Imperial)		2.0"
Width W (Metric)		50.8mm
Height H (Imperial)		1.25"
Height H (Metric)		31.75mm
Material and Specifications		Material
	Material Shortcut	AA

596-00866



Material and Specifications	Adhesive	Ultra High Bond Permanent Acrylic Adhesive
	Halogenfree	Yes
	Operating Temperature	-40°F to +203°F (-40°C to +95°C)
	ROHS Compliant	Yes
	Certification/Specification	NEC2014
	UL Recognized (US)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	5
	Package Quantity (Metric)	5
	Customs Number(Schedule B)	3919905060