

598-00277



Article Number: 598-00277

Description: Thermal Transfer Labels, .25" x 1.5", 16 Across, Cloth, White, 5000/pkg



Base Data		
	Local Order Number	TYHCT-250
	Type	TYHC
	Color	White (WH)
	Features and benefits	<ul style="list-style-type: none"> <li>• Handi-Cards have a split backing so that a portion of the liner can be removed to expose the markers for easy dispensing.</li> <li>• Handi-Cards are kitted on the card so that specific markers can be removed without affecting the other markers on the card.</li> <li>• Markers are pre-printed so no additional post printing is required, saving time and money.</li> <li>• Label material is a conformable cloth that ensures markers stay on wires and cables for the life of the application.</li> </ul>
	Quantity Per	reel
	Product Description	HellermannTyton Handi-Cards are easy release pre-printed cloth markers, on a plastic card, with a strong adhesive for a long lasting bond on wire and cable. The markers are available in Solid format where each marker on the card contains the same legend and Sequence format where each marker on the card contains a different number or letter which is usually printed in sequence from lowest to highest in sort order.
	Short Description	Thermal Transfer Labels, .25" x 1.5", 16 Across, Cloth, White, 5000/pkg
Product Dimensions		
	Length L (Imperial)	1.5"
	Length L (Metric)	38.1mm
	Width W (Imperial)	0.25"
	Width W (Metric)	6.35mm
	Height H (Imperial)	1.50"
	Height H (Metric)	38.10mm
	Bundle Diameter Min. (Imperial)	.13"
	Bundle Diameter Min. (Metric)	3.40mm
	Bundle Diameter Max. (Imperial)	.29"
	Bundle Diameter Max. (Metric)	7.50mm
	Outside Diameter Min. (Imperial)	0.13"

598-00277



Product Dimensions	Outside Diameter Min. (Metric)	3.40mm
	Outside Diameter Max. (Imperial)	0.29"
	Outside Diameter Max. (Metric)	7.50mm
	Horizontal Repeat HR (imperial)	.25"
	Horizontal Repeat HR (metric)	6.35mm
	Print Method	Thermal transfer
	Vertical Repeat VR (imperial)	1.625"
	Vertical Repeat VR (metric)	41.27mm
	Width of Liner WL (metric)	104.70mm
	Width of Liner WL (imperial)	4.12"
Material and Specifications		
	Material	Type 250, Nylon Cloth, white (WH)
	Material Shortcut	250
	Adhesive	Rubber
	Adhesive Operating Temperature	-40°F to +248°F (-40°C to +120°C)
	Minimum Application Temperature	from +50°F (from +10°C)
	Operating Temperature	-40°F to +248°F (-40°C to +120°C)
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	5000
	Package Quantity (Metric)	5000
	Customs Number(Schedule B)	3919102055
	Labels per Column	1
	Labels per Row	16
	Labels per Sheet	48