




$\frac{.219}{5.56} \begin{matrix} \pm.020 \\ \pm.50 \end{matrix}$



FULL SCALE

REDUCED
NO SCALE

$\frac{.500}{12.70}$	$\frac{.063}{1.59}$	20
MAX	MIN	MIN LOOP TENSILE (LBS)
BUNDLE DIA		

HellermannTyton®

ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANN TYTON

name	date	city, state

NOTES

* DIMENSIONS INDICATED WITH AN ASTERISK ARE MEASURED AT THE TANGENCY OF THE TOP RADIUS AND THE SIDE WALL.

REVISION	level	E
DATE	date	11/12/99
BY	by	AAM
ECN #	ECN #	001575
part level	D	

TOLERANCES	.XXXX=	NOTED
	.XXX=	
	.XX=	
	.X=	
	∠=	
	unless otherwise specified	
units	inches/mm	

number	CTT20R	phase	PRODUCTION
name			
			CLAMP TIE
material	NYLON 6/6		
	OR		
	NYLON 6/6 HSO		

FORMAT C	number L	CAD	ACAD	scale	6X
computer file number	CT\CS1\3007001E				
drawn	K.A.C.				
date	11/10/89				
type	CUSTOMER				
number	CT3007001CST				