



Revision level		Revision Record	Changed	Date	Approved	Date
part	drawing					
	02	See ECN 011432	AAC	11/13/09	KAC	11/13/09



PRODUCT CODE DESCRIPTION

T50LDH_UV

COLOR

(CONSULT FACTORY FOR AVAILABLE COLORS)

02

Group Unique Number	Product Code	Cable Range (mm)		Material	A	B	D	E	G	H	Min Loop Tensile Strength (new tons)	
		1 Loop	2 Loops								1st Loop	2nd Loop
-	T50LDH_	1.6 to 101.6	1.6 to 50.8	PA66	1.4 ±0.2	4.7±0.2	6.0±0.5	8.0 ±0.5	395.0 ±10.0	13.7 ±0.9	225	180
-	T50LDH_HS			PA66HS								
-	T50LDH_UV			PA66UV								

SEE CHART

Material


Dimension tolerances unless otherwise specified

.XXXX =
.XXX =
.XX =
.X = NOTED
∠ =

Dimension Units mm

PERFORMANCE SPECIFICATION

ACAD
2004



Drawn
Approved

K.A.C.
K.A.C.

02/15/96
11/13/09

Scale 1:1
Title

Computer File Number
CT\CS\2050005_02

ALL PROPRIETARY RIGHTS IN THE
SUBJECT MATTER SHOWN ON THIS
DRAWING ARE EXCLUSIVE
PROPERTY OF HELLERMANNNTYTON

HellermannTyton

7930 N. Faulkner Rd.
Milwaukee, WI 53224
Ph: (414) 355-1130
Fx: (414) 362-8338

T50LDH
DOUBLE HEAD
CABLE TIE

Drawing-No

CT2050005CST

Format

AH

Sheet 1 of 1