

DATA SHEET

COD. **6101W**

PLANUX WHITE MONITOR

Colour monitor with 3.5" On-Screen Display. With touch-sensitive technology and full-duplex hands-free function. Audio volume, call volume, colour, brightness and contrast adjustment. Ringtones can be customised, selecting from the 7 melodies provided. Backlit control panel consisting of: 1 key button, 1 enable/disable audio button, 1 privacy or doctor function button which can be selected via the menu (with red LED to indicate privacy enabled), 1 self-ignition button, 2 buttons for various uses and 4 buttons for entry, confirmation and navigation within the menus. The monitor, used in conjunction with art. 6112, can be converted into the desk version. Dimensions 145x145x33 mm.



General specifications

Audio system:	No
Audio/video system:	Yes
Flush-mounted:	Yes
Wall-mounted:	Yes
Desk base-mounted:	Yes
Hands-free function:	No
Induction loop function:	No
Type of display:	LCD
Display size (inches):	3,5
Touch screen display:	No
OSD display:	Yes
Display resolution (H x V):	320x240pixel
B/W or colour display:	Color
Product colour:	White RAL9016
Sensitive Touch technology:	Yes
Total buttons:	10
Additional buttons:	1
Backlighting color:	Blue led

Functions

Self-ignition:	Yes
Privacy function:	Yes
Privacy conversation function:	Yes
Key button function:	Yes
Full Duplex hands-free function:	Yes

Hardware specifications

Customisable housing:	Yes
-----------------------	-----

The technical specifications are subject to variations without warning

DATA SHEET

Settings

Loudspeaker volume control:	Yes
Microphone volume control:	Yes
Ringtone volume control:	Yes
Display brightness control:	Yes
Display contrast control:	Yes
Display colour control:	Yes

General info

Product height (mm):	145
Product width (mm):	145
Product depth (mm):	33

Compatibility

Simplebus Top system:	Yes
Simplebus Color system:	Yes

Technical specifications

Maximum current absorption (mA):	200
Operating temperature (°C):	-5 ÷ 40