


Revision level		Revision Record	Changed	Date	Approved	Date
part	drawing					
—	03	See ECN 012383	AAC	06/17/13	KAC	06/17/13



PRODUCT CODE DESCRIPTION

T50IDH UV
 COLOR
 (CONSULT FACTORY FOR AVAILABLE COLORS)


Type	Cable Range (mm)		Material	A	B	D	E	G	H	Min Loop Tensile Strength (newtons)	
	1 Loop	2 Loops								1st Loop	2nd Loop
T50IDH	1.6 to 76.2	1.6 to 38.1	PA66	1.4 ±0.2	4.7±0.2	6.0 ±0.5	8.0 ±0.5	305.0 ±10.0	13.7 ±0.9	225	180
			PA66HS								
			PA66UV								
			PA66HIRHSUV								

SEE CHART

Material

Dimension tolerances unless otherwise specified
 .XXXX =
 .XXX =
 .XX =
 .X = NOTED
 < =
 Dimension Units mm
 PERFORMANCE SPECIFICATION

ACAD MECH
2010



ALL PROPRIETARY RIGHTS IN THE
SUBJECT MATTER SHOWN ON THIS
DRAWING ARE EXCLUSIVE
PROPERTY OF HELLERMANN TYTON

Drawn K.A.C. 02/05/90
 Approved K.A.C. 06/17/13

HellermannTyton

7930 N. Faulkner Rd.
Milwaukee, WI 53224
Ph: (414) 355-1130
Fx: (414) 362-8338

Scale 1:1 Computer File Number CT\CST\2050004_03

Title T50IDH
DOUBLE HEAD
CABLE TIE

Drawing-No Format
CT2050004CST
 Sheet 1 of 1