


Revision level		Revision Record	Changed	Date	Approved	Date
part	drawing					
—	02	See ECN 010831	A.A.C.	08/28/07	K.A.C.	08/28/07



02

Product Code	Cable Range (mm)	Material	Panel Hole Dia	Panel Thickness	A	B	D	E	G	Min Loop Tensile Strength (newtons)
T50SSFM	3.2 to 35	PA6.6	6.0 to 6.6	0.7 to 3.0	1.2 ±0.2	4.6±0.2	5.6 ±0.5	14.7 ±1.5	160.0 ±5.0	225
T50SSFM_HIRHS		PA6.6HIRHS								

SEE CHART
Material
Dimension tolerances unless otherwise specified .XXXX = ± .0130 .XXX = ± .130 .XX = ± .30 .X = ± .8 ∠ = ± 0.5 °
Dimension Units mm
PERFORMANCE SPECIFICATION

ACAD MECH 2008		Drawn A.A.C. 02/15/07 Approved K.A.C. 08/28/07	Scale 1:1 Computer File Number CT\CST\CT07-004-002_02
ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANN TYTON		HellermannTyton 7930 N. Faulkner Rd. Milwaukee, WI 53224 Ph: (414) 355-1130 Fx: (414) 362-8338	T50SSFM WING PUSH MOUNT TIE
		Drawing-No CT07-004-002CST	Format AH Sheet 1 of 1