





SECTION B-B




SECTION A-A

- PERFORMANCE REQUIREMENTS:
- * FIR TREE MOUNTS INTO .520 +/- .020" HOLES
 - * PANEL THICKNESS RANGE IS FROM .075 TO .515"
 - * FIR TREE PULL OUT FORCE IS GREATER THAN 140lbs IN A .520" HOLE AND A SHEET METAL THICKNESS OF .237"



SCALE 5/4



SECTION C-C
SCALE 5/4

INVENTORS

HellermannTyton®

ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANN TYTON

name	date	city, state
GERRY GEIGER	1/2/98	JACKSON WI

REVISION

level	by	date	ECN #	part level
05	GGG	1/9/12	012007	C

DIMENSIONS

units	inches
.XXXX= ±0.005/[1,127]	
.XXX= ±0.010/[1,25]	
.XX= ±0.02/[1,5]	
.X= ±0.1/[2,5]	
∠= ±0.5	
unless otherwise specified	

PART

number	phase	PRODUCTION
S3STM50		
name	STANDOFF 3-WAY SADDLE with 1/2" FIR TREE MOUNT	
material	NYLON 6/6 IMPACT MODIFIED, HEAT STABILIZED BLACK	

DRAWING

FORMAT	AH version	J	CAD	PRO-E	scale	1/1
computer file number						previous number
drawn	G GEIGER	checked	K Christian	approved		
date	1/2/98	checked	1/9/12	approved		
type	CUSTOMER					sheet 1 of 1
number	MT2022009CST					