







PERFORMANCE REQUIREMENTS:

1. FIR TREE PUSH IN FORCE: 15LBS MAX IN A 6.6MM HOLE AND A SHEET METAL THICKNESS OF 1.8MM
2. FIR TREE PULL OUT FORCE: 50LBS MIN IN A 6.6MM HOLE AND A SHEET METAL THICKNESS OF 1.8MM
3. HOLE DIAMETER RANGE: 6.5MM- 7.2MM
4. PANEL THICKNESS RANGE: .6MM - 8.5MM
5. CABLE TIE TENSILE STRENGTH: 50LBS MIN
6. MINIMUM BUNDLE DIAMETER: 1.6MM
7. MAXIMUM BUNDLE DIAMETER: 50MM



IN
V
E
N
T
O
R
S

HellermannTyton

ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANN TYTON

name	date	city, state

RE
V
I
S
I
O
N

level	04
by	JJP
date	02/04/2009
ECN #	011234
part level	B/C

D
I
M
E
N
S
I
O
N
S

.XXXX = [±.127]/±0.005
.XXX = [±.25]/±0.01
.XX = [±.5]/±0.02
.X = [±6.4]/±0.25
∠ = ±0.5°
unless otherwise specified
units [millimeters]/inches

P
A
R
T

number	T50ROSFT6LGU	phase 04	Production
name	CIRCULAR FIR TREE CABLE TIE		
material	NYLON 6/6 HS BLACK		

D
R
A
W
I
N
G

format version N	AH	CAD	SW 2007	scale	2:1
computer file name		previous drawing number			
ct06-027-011CST_04					
drawn	JJP	checked	approved		
	03/07/2007				
type	Customer		sheet 1 of 1		
number	CT06-027-011CST				