





- 04 PERFORMANCE REQUIREMENTS (DAM):**
1. .25" STUD PUSH ON FORCE: 20LBS MAX
 2. .25" STUD PULL OFF FORCE: 40LBS MIN
 3. CABLE TIE TENSILE STRENGTH: 120LBS MIN
 4. MINIMUM BUNDLE DIAMETER: .375"
 5. MAXIMUM BUNDLE DIAMETER: 2.25"

INVENTORS

HellermannTyton®

ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANN TYTON

name	date	city, state

REVISION	level	04
	by	JJP
	date	08/25/2008
	ECN #	010951
	part level	A/C

DIMENSIONS	TOLERANCES	.XXXX = $[\pm .127] / \pm 0.005$
		.XXX = $[\pm .25] / \pm 0.01$
		.XX = $[\pm .5] / \pm 0.02$
		.X = $[\pm 6.4] / \pm 0.25$
		$\angle = \pm 0.5^\circ$
		unless otherwise specified
	units	[millimeters]/inches

PART

number	WSS250	phase	Production
name	WIDE STRAP TIE W/ .25" STUD MOUNT		
material	NYLON 6/6, IMHSUV BLACK		

DRAWING	format	AH	CAD	SW 2007	scale	3:2
	version N					
	computer file name	CT06-026-002CST_04			previous drawing number	
	drawn	JJP	checked	GGG	approved	
		01/16/2007		08/09/2007		
	type	Customer			sheet 1 of 1	
	number	CT06-026-002CST				