




SW2014



Revision level			Revision Record	Changed	Date	Approved	Date
Drawing	State	Part					
00.0	Design Release		SEE ECN# 013599	GRW	10/26/2016	KAC	10/26/2016



Conduit Size		Euro Size	HellermannTyton Part Number	Manufacturer Reference Number	Style	Dimension															
						A		B		C		D		E		F		G		H	
in.	mm	(NW)				in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm
3/8	16	12	HG038-SFL	FPA16-FL	A	1.18	30	1.77	45	1.61	41	1.14	29	0.57	14.5	1.42	36	NA	NA	0.21	5.2
1/2	21	17	HG050-SFL	FPA21-FL	A	1.18	30	1.77	45	1.73	44	1.33	34	0.57	14.5	1.42	36	NA	NA	0.21	5.2
3/4	28	23	HG075-SFL	FPA28-FL	A	1.50	38	2.52	64	1.93	49	1.73	44	0.77	19.5	2.09	53	NA	NA	0.24	6.2
1.00	34	29	HG100-SFL	FPA34-FL	B	2.60	66	2.32	59	2.17	55	2.01	51	1.04	26.5	1.42	36	2.13	54	0.24	6.2
1.25	42	36	HG125-SFL	FPA42-FL	B	2.60	66	2.32	59	2.48	63	2.48	63	1.65	42.0	1.42	36	2.13	54	0.24	6.2

Material
PA66

Units: inches

Dimension without
tolerances details to:
.xxxx = ±.0005
.xxx = ±.005
.xx = ±.01
.x = ±.03
None = ±.06
∠ = ±0.5°
Dimension Formatted in[mm]

The copyright of this
drawing is reserved by
HellermannTyton. It is
issued on condition that it is
not reproduced, copied, or
disclosed to a third party,
either wholly or in part,
without the consent of
HellermannTyton.

Drawn

GRW

10/26/2016

Approved

KAC

10/26/2016

HellermannTyton

North America
Email: corp@htamericas.com
Web: www.hellermann.tyton.com

Article/Type-No HG-SFL SERIES

Title **HELAGUARD STRAIGHT NYLON
SWIVEL FLANGE FITTING, IP66**

Drawing-No

PRODUCTION : Phase

15-0839-001-CSU

Scale 1:1

Project Number

PRP 15-0839

Format AH

Sheet 1/1