




SW2014



Revision level			Revision Record	Changed	Date	Approved	Date
Drawing	State	Part					
00.0	Design Release		SEE ECN# 013639	GRW	12/1/2016	KAC	12/1/2016



NOTES:

1. OPERATING TEMPERATURE
-58° F TO +275° F (-50° C TO +135° C)
2. RoHS
3. HF
4. IP RATING IP68 + IP67 + IP68 + IP69
5. FITS WITH UL360 SIZES
6. FLAMMABILITY SELF-EXTINGUISHING (EN 61386)
7. UL LISTED TO UL514B
8. PULL-OFF TENSILE STRENGTH 265 LBS (120KG)

Conduit Size		HellermannTyton Part Number	Manufacturer Reference Number	Dimension (mm)							
				A		B		C		D	
				in	mm	in	mm	in	mm	in	mm
1/2	20.0	LTP20-LTP20	LTP20-LTP20	1.56	39.5	1.14	29	0.57	14.5	1.02	26.0
3/4	25.0	LTP25-LTP25	LTP25-LTP25	1.85	46.9	1.38	35	0.71	18	1.30	33.0
1	32.0	LTP32-LTP32	LTP32-LTP32	2.20	56	1.65	42	0.97	24.6	1.57	40.0
1-1/4	40.0	LTP40-LTP40	LTP40-LTP40	2.48	63	2.05	52	1.29	32.7	1.97	50.0

Material NICKEL PLATED BRASS	Units: inches Dimension without tolerances details to: .xxxx = ±.0005 .xxx = ±.005 .xx = ±.01 .x = ±.03 None = ±.06 ∠ = ±0.5° Dimension Formatted in [mm]	The copyright of this drawing is reserved by HellermannTyton. It is issued on condition that it is not reproduced, copied, or disclosed to a third party, either wholly or in part, without the consent of HellermannTyton.	Drawn	GRW	12/1/2016	Article/Type-No LTP-LTP SERIES			Scale
			Approved	KAC	12/1/2016	Title HELAGUARD STRAIGHT COMPRESSION COUPLER FITTING FOR LTP METALLIC CONDUIT WITH LIQUID-TIGHT COVER			Project Number PRP 16-1972
			HellermannTyton North America Email: corp@htamericas.com Web: www.hellermann.tyton.com			Drawing-No PRODUCTION : Phase			Format AH
						16-1972-001-CSU			Sheet 1/1