






SW2015



Revision level			Revision Record	Changed	Date	Approved	Date
Drawing	State	Part					
00.0	Design Release		SEE ECN# 013695	GRW	1/26/2017	KAC	1/26/2017

**NOTES**

1. WEIGHT: 3 LBS
2. BLADE THICKNESS: .032"
3. 110 VOLTS
4. OPERATING TEMPERATURE: 1112°F (+600°C)



Material ASSEMBLED	Units: inches	<div>The copyright of this drawing is reserved by HellermannTyton. It is issued on condition that it is not reproduced, copied, or disclosed to a third party, either wholly or in part, without the consent of HellermannTyton.</div>	Drawn	GRW	1/26/2017	Article/Type-No BSBHK	Scale	
	Dimension without tolerances details to: .xxxx = ±.0005 .xxx = ±.005 .xx = ±.01 .x = ±.03 None = ±.06 ∠ = ±0.5° Dimension Formatted in/[mm]		Approved	KAC	1/26/2017	Title BENCH MOUNT HOT KNIFE FOR BRAIDED SLEEVING	Project Number PRP 17-0423	
			<div>HellermannTyton</div> <div>North America</div> <div>Email: corp@htamericas.com</div> <div>Web: www.hellermann.tyton.com</div>			Drawing-No	Production : Phase	Format AH
						17-0423-001-CSU		Sheet 1/1