


REDUCED
NO SCALE

① CATALOG NUMBER		PANEL THICKNESS	A		B		C		D		E	
MATERIAL	SIZE		MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN
FP	AA	.016 - .035	.100	.080	.040	.034	.045	.025	.085	.060	.020	.000
FP, FH, FT	A	.016 - .051	.165	.145	.071	.051	.070	.050	.120	.095	.020	.000
FP, FH, FT	B	.051 - .083	.190	.170	.105	.085	.070	.050	.120	.095	.020	.000
FP, FH, FT	C	.083 - .130	.235	.215	.122	.126	.070	.050	.120	.095	.020	.000
FP, FH, FT	D	.130 - .189	.340	.319	.210	.190	.085	.065	.180	.155	.030	.000
FP, FH, FT	E	.189 - .256	.400	.380	.275	.255	.085	.065	.190	.165	.030	.000
FP, FT	F	.256 - .319	.460	.440	.335	.315	.090	.070	.200	.175	.030	.000
FH		.256 - .319	.460	.437	.335	.315	.090	.070	.200	.165	.030	.000
FP, FT	G	.319 - .382	.530	.510	.406	.386	.090	.070	.200	.175	.030	.000
FH		.319 - .382	.530	.506	.406	.386	.090	.070	.200	.165	.030	.000
FP, FT	H	.382 - .508	.655	.635	.530	.510	.090	.070	.200	.175	.030	.000
FH		.382 - .508	.655	.630	.530	.510	.090	.070	.200	.165	.030	.000

INVENTORS

HellermannTyton

ALL PROPRIETARY RIGHTS IN THIS SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANNTYTON

name	date	city, state

NOTES

① SAMPLE PART NUMBER

FPAA
SIZE
MATERIAL

REVISION
level
by
date 12/11/97
ECN # 000389
part level

DIMENSIONS
TO LUNGS JOINTS
.XXXX=
.XXX=.005
XX=
.X=
Z=
unless otherwise specified
units inches

PART
number
name
GROMMET
material
FP = POLYETHYLENE
FH = NYLON
FT = P.T.F.E. (TEFLON)

FORMAT B version J
computer file number
GR\SERV\2000000B
previous number
GR2000
date 12/11/97
type SERIES
sheet 1 of 1
number GR2000000SER