

# S6000 Spectra™ Series - S6000-101

## Exit Check® - Delayed Egress All-In-One



The EXIT CHECK® ALL-IN-ONE device integrates our premium Spectra™ bar with SDC's innovative delayed egress electronics.

### FEATURES

When unauthorized egress is initiated by depressing the push pad of the S6000-101, an audible alarm will sound and an irreversible delay period of 15 seconds will begin. After the delay period has expired, the device unlocks, permitting egress until the device is reset. In a life safety emergency, the device will immediately unlock upon loss of power or when powered by a fire control supervised power supply.

- Low Power consumption 540 mA @24VDC
- 15 second exit delay, 1 or 2 second nuisance delay
- Built-in Visual and Audible Annunciation
- Single or pair of doors
- Key reset, bypass (Mortise cylinder not included)
- Field-selectable 1 to 30 second request-to-exit, anti-tailgate and door prop alarm
- UL Listed





MODELS	
<b>S6100-101</b>	Rim Mount
<b>S6200-101</b>	Surface Vertical
<b>S6300-101</b>	Mortise
<b>S6800-101</b>	Concealed Vertical





## APPLICATION

- Restricting the egress of wandering patients for their own safety
- Restricting the egress of commercial center patrons for security application needs
- Controlling pedestrian traffic in transportation facilities, including airport jetways and tarmacs
- Reducing shoplifting and employee theft



PRODUCT SKU SAMPLE: **S61 03 P U 36 101 NC EKE03U**



## HOW TO ORDER

### 1| SPECIFY DEVICE

- S61** Rim Mount
- S62** Surface Vertical - ROD GUARDS SUGGESTED (by others)
- S63** Mortise [03 Lever Trim included] - specify: **EE/GE**
- S68** Concealed Vertical

### 2| SPECIFY FUNCTION

- 01** Exit Only (No Trim)
- 02** Dummy
- 03** Nightlatch Lever, Key Latch Retraction

### 3| SPECIFY PANIC OR FIRE RATED

- P** Panic
- F** Fire

### 3A| SPECIFY HAND (S63 MORTISE ONLY)

- LR** Left hand reverse bevel, LHRB
- RR** Right hand reverse bevel, RHRB

### 4| SPECIFY FINISH

- U** 630 Dull Stainless Steel (standard)

### 5| SPECIFY LENGTH

- 36** For 36" Doors (standard)
- 42** For 42" Doors
- 48** For 48" Doors

### 6| SPECIFY DELAYED EGRESS

- 101** Electrification of master exit device and integrated controller with key switch control and reset, less cylinder
- DES** For pair of doors, additional exit device equipped with delayed egress mechanism, less integrated controller. **Must be ordered together with 101 device.**

### 7| SPECIFY OPERATIONS

- NC** IBC, IFC, NFPA 101, NFPA 1-UFC, UBC, SBC Compliant  
Fixed 15 exit delay, 1 or 2 second nuisance delay  
Calif. Building Code OSHPD/Manual Power Up
- ND** IBC, IFC, NFPA 101, NFPA 1-UFC, UBC, SBC Compliant  
Fixed 15 exit delay, 1 or 2 second nuisance delay
- BC** BOCA National Building Code and Chicago Building Code Compliant  
15 second fixed exit delay, 0 second nuisance delay, auto reset 30 seconds after door closure
- BD** BOCA National Building Code  
15 second fixed exit delay, 1 or 2 second nuisance delay, auto reset 30 seconds after door closure

### 8| SPECIFY TRIM (OPTIONAL)

**S61 RIM, S62 SURFACE AND S68 CONCEALED VERTICAL ONLY**

Mechanical Trim (less cylinder)

- EK02U** Dummy Eclipse Escutcheon
- GK02U** Dummy Galaxy Escutcheon
- EK03U** Eclipse Escutcheon
- GK03U** Galaxy Escutcheon

Electric Trim

- Failsecure, field reversible to failsafe
- 4 ft cable
- 600/300 mA @12/24VDC

**EKE03U** Eclipse style electric trim less mortise cylinder, Stainless Steel Finish

**GKE03U** Galaxy style electric trim less mortise cylinder, Stainless Steel Finish

### SPECIFY TRIM OPTIONS:

Rim Cylinder Required for 03 function, Mortise Cylinder Required for S6300

**CYL-6KDDQ** 6 pin, 1.125" Mortise Cylinder, Keyed Different, Dull Chrome

**CYL-6KAQ** 6 pin, 1.125" Mortise Cylinder, Keyed Alike, Dull Chrome

**RIM-CYL-KA** 6-pin Rim Cylinder, Keyed Alike, Specifically For EK03, GK03