

P600	SCH 80	6.625	5.657	0.432	0.484	3.6545	0.950	0.458
------	--------	-------	-------	-------	-------	--------	-------	-------

Standard Specifications for Corrugated Petroduct

Product Part #	SDR/SCH Rating	Nominal O.D.	Min. I.D.	Min. Wall	Max. Wall	Weight LBS/FT.	Mean Density	Mean Wall
PC100	N/A	1.300	1.000	0.020	0.040	0.0765	0.950	0.030
PC100-FR	N/A	1.300	1.000	0.020	0.040	0.0816	0.950	0.030
PC125	N/A	1.540	1.250	0.020	0.040	0.1030	0.950	0.030
PC125-FR	N/A	1.540	1.250	0.020	0.040	0.1022	0.950	0.030
PC150	N/A	1.900	1.500	0.025	0.040	0.1251	0.950	0.035
PC200	N/A	2.375	2.000	0.025	0.045	0.1754	0.950	0.035

Standard Specifications for Ribbed Petroduct

Product Part #	SDR/SCH Rating	Nominal O.D.	Min. I.D.	Min. Wall	Max. Wall	Weight LBS/FT.	Mean Density	Mean Wall
PR100-2	17	1.315	1.091	0.077	0.097	0.1437	0.950	0.087
PR100-2	13.5	1.315	1.051	0.097	0.117	0.1727	0.950	0.107
PR100-2	11	1.315	1.005	0.120	0.140	0.2048	0.950	0.130
PR100-2	9	1.315	0.953	0.146	0.166	0.2394	0.950	0.156
PR118-2	15.5	1.420	1.166	0.092	0.112	0.1799	0.950	0.102
PR118-2	13.5	1.420	1.140	0.105	0.125	0.2002	0.950	0.115
PR125-2	17	1.660	1.394	0.098	0.118	0.2369	0.950	0.108
PR125-2	13.5	1.660	1.310	0.125	0.145	0.2708	0.950	0.135
PR125-2	11.5	1.660	1.272	0.144	0.164	0.3061	0.950	0.154
PR125-2	11	1.660	1.258	0.151	0.171	0.3203	0.950	0.161
PR125-2	SCH 40	1.660	1.310	0.140	0.160	0.3098	0.950	0.150
PR150-2	17	1.900	1.586	0.112	0.132	0.3107	0.950	0.122
PR150-2	13.5	1.900	1.518	0.141	0.161	0.3717	0.950	0.151
PR150-2	11	1.900	1.444	0.173	0.194	0.4145	0.950	0.183
PR150-2	SCH 40	1.900	1.520	0.145	0.165	0.3800	0.950	0.155
PR200-2	17	2.375	1.995	0.140	0.160	0.4418	0.950	0.150
PR200-2	13.5	2.375	1.921	0.176	0.197	0.5368	0.950	0.186
PR200-2	11	2.375	1.831	0.216	0.242	0.6458	0.950	0.229
PR200-2	SCH 40	2.375	1.967	0.154	0.174	0.4792	0.950	0.164

Product Part #	SDR Rating	Nominal O.D.	Min. I.D.	Min. Wall	Max. Wall	Weight LBS/FT.	Mean Density	Mean Wall
PR100-2	13	1.270	1.008	0.091	0.111	0.1582	0.950	0.101
PR125-2	11.5	1.660	1.320	0.120	0.140	0.2673	0.950	0.130
PR125-2	9	1.700	1.294	0.153	0.173	0.3292	0.950	0.163