

960H Corner Mount Color Camera



CVC605CM

3.6mm lens - optional lenses available, stainless steel housing

Features

- 1/3" Sony Super HAD II™ color CCD
- 700 TV lines of resolution
- Also available in brass housing
- 92° corner mount camera
- Perfect for elevators, hallways, etc.
- 5 year warranty

960



Specifications

Image Sensor	1/3" Sony Super HAD II™ color CCD
Resolution	700 TV lines
Effective Pixels	976 (H) x 494 (V)
Total Pixels	1020 (H) x 508 (V)
Minimum Illumination	0.001 lux (sense-up on)
Electronic Shutter	1/60 sec. – 1/100,000 sec.
S/N Ratio	More than 46dB
Video Output	1.0Vp-p / 75 ohms
Power Consumption	230mA (color), 90mA (BW)
Power Supply	12VDC regulated (UL & CSA listed power supply included)
Operating Temperature	14° F – 122° F
Housing	18 gauge stainless steel with lexan window
Dimensions	9" (W) x 7" (H) x 4" (L)
Weight	1.4 lbs.

Optional Lenses

CVC605CM2.2	2.2mm lens	CVC605CM2.9	2.9mm lens
CVC605CM2.5	2.5mm lens		

Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 6/27/14