

# SF117/2C, SF117/4C Emergency Switch

## IL178 Specification Sheet

CM800 Emergency Call Systems • Rev. 15 - 10/2016

### Features

- Single-gang mounting
- 2 or 4 pole switches
- Attractive, flame-retardant (UL® 94V-0) plastic panel
- Highly visible emergency labeling
- May use with a central annunciator, or for local alarm functions

### Description

The SF117-series Emergency Call Switch is available in two models and features a rugged, long-life, positive-acting switch mounted on a durable flame-retardant (UL® 94V-0) plastic panel. Signaling an emergency requires just a short pull in any direction on the 6' long nylon cord. The signal cannot be canceled except at the point of origin. The SF117/2C provides two circuits to operate a separate visual and audible signal. The SF117/4C provides two additional circuits that may be used to operate additional signaling devices as needed.

### Specifications

Dimensions:	Height:	4.5"	(114 mm)
	Width:	2.75"	(70 mm)
	Depth:	1.5"	(38 mm)
Panel:	Flame-retardant (UL® 94V-0) plastic		
Switch:	SF117/2C—2PDT SF117/4C—4PDT		
Connection:	Wire leads		
Mounting:	Standard single-gang electrical box		
Marking:	Pad-printed <b>EMERGENCY</b>		



SF117/2C, SF117/4C Emergency Switch

### Required Components

#### Standalone:

SS106 Transformer  
LI381 or LI123B Corridor Dome Light

#### System:

CM800 Emergency Call System