



VZ-215LED-SN ADVANTAGES

- 21.5" 1080p HD Resolution
- HDMI, DVI, VGA, **HD-SDI**, COMPONENT (**BNC Type**)
- Blue Mono, H/V Delay, Built-in 2 Speakers
- SDI Embedded 16ch Audio Level Meter / 2ch Select Audio Waveform
- Marker / Safety Area / Corner
- Scan - Zero, Over and pixel to pixel
- DPMS Select
- 2-Year Warranty




MODEL #		VZ-215LED-SN
VIDEO		
Screen Size		21.5"
Max. Resolution		1920 x 1080 @60Hz
Pixel Pitch		0.24825 mm x 0.24825 mm
Brightness		250cd/m ² (Typical)
Contrast Ratio		1000:1
Aspect Ratio		16 : 9
Viewing Angle (H/V)		170° / 160°
Display Color		16.7 Million
Response Time		< 5ms
Frequency (H)		31 ~ 80 kHz
Frequency (V)		56 ~ 75 Hz
INTERFACE		
Component (BNC) In		3
3G-SDI In / Out (BNC, 1 input / loop-through out)		1 / 1
VGA In (15Pin D-Sub)		1
DVI In		1
HDMI In		1
RJ45 In		1
PGM (HDMI) In		1
PC Stereo In		1
AUDIO		
Built in speaker		2W X 2
DIMENSIONS & WEIGHT		
Outline Dimension (W x H x D)		20.25 " x 14.56 " x 1.77"
		514.5 mm x 370 mm x 44.958 mm
Net Weight		8.4 lbs (3.8 kg)
MOUNT		
VESA		100mm x 100mm, M4 x L10 Screws
GENERAL		
Power	Electrical Ratings	DC12V (AC100 ~ 240V[50/60Hz])
	Consumption	24 W
Warranty	Parts/ Labor	2 Year / 3 Year
	MTBF (Approx.)	30,000 Hours
Operating Temperature		32 - 104°F / 0 - 40°C
Regulations		TBD
Compatible Mounts	WALL	VZ-WM05, VZ-WM11, VZ-AM01
	CEILING	VZ-CMKIT-01, VZ-CMKIT-02
	RACK	VZ-RMK08

INPUT FORMAT		
SDI	SMPTE 425M-A (YCbCr 4:2:2)	1080p (60/59.94/50)
	SMPTE 274M (YCbCr 4:2:2)	1080i (60/59.94/50)
		1080p (30/29.97/25/24/23.98)
		1080Psf (30/29.97/25/24/23.98)
	SMPTE 296M (YCbCr 4:2:2)	720P(60/59.94/50/30/29.97/25/24/23.98)
	SMPTE 125M (YCbCr 4:2:2)	525i (NTSC 59.94)
ANALOG	ITU-R BT.601 (YCbCr 4:2:2)	625i (PAL 50)
	2K Format (YCbCr 4:2:2)	2048 x 1080P (24/23.98/24sF/23.98sF)
	COMPONENT	1080P (60/59.94/50, 30/29.97/25/24/23.98)
HDMI		1080i (60/59.94/50), 720P(60/59.94/50)
DVI		480i/480P/576i/576P/1080i/1080P
VGA		VGA, SGA, XGA, SXGA, WXGA, WUXGA
SPECIAL FEATURES		
Line Marker Option		16:9, 4:3, 4:3(on air), 15:9, 14:9, 13:9, 1.85:1, 2.35:1, 1.85:1 & 4:3
Safety Area Option		Off, 80%, 85%, 88%, 90%, 93% and 100%
SDI Sound Channel Option		CH1, CH2, CH1+CH2, CH3, CH4, CH3+CH4, CH5, CH6, CH5+CH6, CH7, CH8, CH7+CH8, CH9, CH10, CH9+CH10, CH11, CH12, CH11+CH12, CH13, CH14, CH13+CH14, CH15, CH16, CH15+CH16
RGB Gain		-128 to 128
RGB Bias		-50 to 50


Contact ViewZ

- Address : 177 W. Orangethorpe Ave., Placentia, CA 92870
- Phone : (714) 996-1177, Fax : (714) 996-1138
- Sales : sales@viewzusa.com
- Specification subject to change without notice.

DIMENSIONS



INTERFACE



1. DC12V IN
2. 3G-SDI IN / OUT
3. HDMI IN
4. DVI IN
5. VGA IN
6. YPbPr In
7. PC STEREO IN
8. PGM
9. RS422 IN

Contact ViewZ

- Address : 177 W. Orangethorpe Ave., Placentia, CA 92870
- Phone : (714) 996-1177, Fax : (714) 996-1138
- Sales : sales@viewzusa.com
- Specification subject to change without notice.