

RV6PPA2U48XX Faceplates and Panels - CAT6+ REVConnect Patch Panel, Angled 2U48-Port



For more Information  
please call  
  
1-800-Belden1



General Description:

CAT6+ REVConnect Patch Panel, Angled, 48-Port, 2U (Preloaded)

Image

Image:



Usage (Overall)

Suitable Applications:	2400, 3600, 4800 Systems, TIA Category 6+, ISO Class E, 1GBASE-T
Related Parts:	CAT6+ REVConnect Jacks, CAT6+ Modular Cords

Physical Characteristics (Connectivity)

Capacity	
Max. Capacity:	48 connectors (preloaded)
Access	
Front Connection:	Flush
Termination Area:	Front and Rear

Dimensions	
Dimensions:	
Height (in.)	Width (in.) Depth (in.)
3.470	19.000 5.830

Materials		
Materials:		
Description	Material	Color

## RV6PPA2U48XX Faceplates and Panels - CAT6+ REVConnect Patch Panel, Angled 2U48-Port

Panel	Steel	Black/White
Frame	PC/ABS	Black/White
Management Bar	Steel	Black
Clear Window	Polycarbonate	Transparent

**Color**

Color: Black, White

**Weight**

Weight: 3.326 lbs.

**Included Parts**

Included Parts: 48 Cat6+ REVConnect Jacks Black preloaded; 50 REVConnect Cores; 4 Screws (10x32); 4 Screws (12x24); 2 Velcro Straps; 8 Clear Windows; 2 Rear Cable Management Bar; 1 Installation Guide

**Packaging**

Packaging: Individually packaged in a cardboard box.

**Mechanical Characteristics (Connectivity)**

Footprint/Type: KeyConnect

Plug / Jack Compatibility: RJ45

**Termination Interface:**

Termination	Connection	Durabilities
Front	Mated Connection	750 cycles
Rear	Mated Connection	20 cycles

Cable/Connector Retention: 15 lbs.

Connector/Hardware Retention: 20 lbs.

Plug/Connector Retention: 11.250 lbs.

Storage Temperature Range: -40°C To +70°C

Installation Temperature Range: -10°C To +60°C

Operating Temperature Range: -10°C To +60°C

Tool Compatibility: REVConnect Termination Tool (RVUTT01)

**Applicable Specifications and Agency Compliance (Overall)****Applicable Standards & Environmental Programs**

UL Rating: UL94V-0

IEEE Specification: Power Over Ethernet (PoE) IEEE 802.3at type 1 and 2 (up to 30W), IEEE802.3bt/D1.7 type 3 and 4 (up to 100W), CISCO UPOE (up to 60W), Power over HDBase TTM (up to 100W)

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 07/01/2006

MIL Order #39 (China RoHS): EUP 50

Telecommunications Standards: Category 6 - TIA 568.C.2, Category 6 - ISO/IEC 11801:2002 Ed.2

Safety Listing: c(UL)us Listed

Other Specification: UL 1863, IEC 60603-7, FCC part 68-F

**Suitability**

Suitability - Indoor: Yes

**Transmission Characteristics (Connectivity)**

Mated Connection Table 1:

Frequency (MHz)	Max. Insertion Loss TIA* (dB)	Max. Insertion Loss Belden** (dB)	Min. NEXT TIA* (dB)	Min. NEXT Belden** (dB)	Min. FEXT TIA* (dB)	Min. FEXT Belden** (dB)
1.000	0.100	0.100	75.000	77.000	75.000	77.000
4.000	0.100	0.100	75.000	77.000	71.100	75.100
8.000	0.100	0.100	75.000	77.000	65.000	69.000
10.000	0.100	0.100	74.000	77.000	63.100	67.100
16.000	0.100	0.100	69.900	72.900	59.000	63.000
20.000	0.100	0.100	68.000	71.000	57.100	61.100
25.000	0.100	0.100	66.000	69.000	55.100	59.100
31.250	0.110	0.100	64.100	67.100	53.200	57.200
62.500	0.160	0.120	58.100	61.100	47.200	51.200
100.000	0.200	0.160	54.000	57.000	43.100	47.100
200.000	0.280	0.240	48.000	51.000	37.100	41.100

## RV6PPA2U48XX Faceplates and Panels - CAT6+ REVConnect Patch Panel, Angled 2U48-Port

250.000	0.320	0.280	46.000	49.000	35.100	39.100
300.000		0.310		44.500		37.600

Mated Connection Table - Footnote:

\* TIA/EIA-568-C.2 Category 6 Standard. \*\* Worst-case performance for a CAT6+ mated connection using CAT6+ modular plugs.

Mated Connection Table 2:

Frequency (MHz)	Min. Return Loss TIA* (dB)	Min. Return Loss Belden** (dB)	Min. Balanced TCL TIA* (dB)	Min. Balanced TCL Belden** (dB)
1.000	30.000	34.100	40.000	42.000
4.000	30.000	34.100	40.000	42.000
8.000	30.000	34.100	40.000	42.000
10.000	30.000	34.100	40.000	42.000
16.000	30.000	34.100	40.000	42.000
20.000	30.000	34.100	40.000	42.000
25.000	30.000	34.100	40.000	42.000
31.250	30.000	34.100	38.100	42.000
62.500	30.000	34.100	32.100	36.100
100.000	28.000	30.000	28.000	32.000
200.000	22.000	24.000	22.000	26.000
250.000	20.000	22.000	20.000	24.000
300.000	18.500	20.500		22.500

**Dielectric Strength:** 1,000 V RMS @ 60 Hz for 1 minute (Signals to Ground)

**Current Rating:** 1.300 A

**Insulation Resistance:** 500 M-Ohm Minimum

**Max. Contact Resistance:** 20 m-Ohm

**Termination Resistance:** 2.5 m-Ohm

### Notes (Overall)

**Notes:** For proper installation refer to Installation Guide PX106520 included with the product or visit our web site at <http://www.belden.com>

### Product Family

Part Numbers:

Item Number	Description
RV6PPF1U24BK	CAT6+ REVConnect Patch Panel Flat 1U24-Port, Black (Preloaded)
RV6PPF1U24WH	CAT6+ REVConnect Patch Panel Flat 1U24-Port, White (Preloaded)
RV6PPA1U24BK	CAT6+ REVConnect Patch Panel Angled 1U24-Port, Black (Preloaded)
RV6PPA1U24WH	CAT6+ REVConnect Patch Panel Angled 1U24-Port, White (Preloaded)
RV6PPF2U48BK	CAT6+ REVConnect Patch Panel Flat 2U48-Port, Black (Preloaded)
RV6PPF2U48WH	CAT6+ REVConnect Patch Panel Flat 2U48-Port, White (Preloaded)
RV6PPA2U48BK	CAT6+ REVConnect Patch Panel Angled 2U48-Port, Black (Preloaded)
RV6PPA2U48WH	CAT6+ REVConnect Patch Panel Angled 2U48-Port, White (Preloaded)

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 0 Revision Date: 06-20-2017

© 2017 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.