

ZCE10

limit switch head ZCE - metal end plunger

Product availability : Stock - Normally stocked in distribution facility



Price* : 7.80 USD



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product compatibility	XCKT XCMD XCKP XCKD
Associated body	ZCMD37L2 ZCP25 ZCP37 ZCMD25L2 ZCP28 ZCMD61C12 ZCMD21L5 ZCT27N12 ZCMD39L5 ZCMD21L08U78 ZCMD21L1 ZCMD21L2 ZCP21 ZCMD21L08R12 ZCMD81L2 ZCP29M12 ZCMD41L2 ZCMD81L5 ZCT27P16 ZCP39 ZCD26 ZCMD21M12 ZCD28 ZCT27G11 ZCT21G11 ZCT28G11 ZCD35 ZCMD81L1

ZCMD29L2
 ZCMD29L5
 ZCP31
 ZCT25G11
 ZCT25P16
 ZCD21
 ZCMD41L5
 ZCD29
 ZCMD37L5
 ZCMD69C12
 ZCT21P16
 ZCT28N12
 ZCMD29C12
 ZCD37
 ZCMD39L1
 ZCMD25L5
 ZCT26P16
 ZCT28P16
 ZCMD29L1
 ZCT21N12
 ZCD29M12
 ZCD27
 ZCD31
 ZCD25
 ZCMD37L1
 ZCT26G11
 ZCMD21C12
 ZCMD25L1
 ZCT26N12
 ZCP29
 ZCP21M12
 ZCD39
 ZCT25N12
 ZCMD61M12
 ZCP26
 ZCP35
 ZCMD41L1
 ZCD21M12
 ZCMD39L2
 ZCP27

Movement of operating head	Linear
Type of operator	End plunger spring return metal
Type of approach	Vertical approach 1 direction

Complementary

Positive opening	With
------------------	------

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22413 - LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	00785901449980
Nbr. of units in pkg.	1
Package weight(Lbs)	0.02
Returnability	Y
Country of origin	ID

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0851 - Schneider Electric declaration of conformity

REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------