

**1-1711091-2****RJ45 Patch Cord, category 6, unshielded, white, 1.5 m**

## Body Features

|              |       |
|--------------|-------|
| Cable Color  | White |
| Shield Style | UTP   |

## Configuration Features

|                           |              |
|---------------------------|--------------|
| Configuration             | Double-ended |
| Keyed                     | No           |
| Number of Positions       | 4-pair       |
| Number of Power Positions | 0            |

## Dimensions

|                                |                               |
|--------------------------------|-------------------------------|
| Length                         | 1.50 m   4.92 ft              |
| Overall Outside Cable Diameter | 5.588 mm   0.220 in           |
| Wire Size (CMA)                | .205 mm <sup>2</sup>   24 AWG |

## Industry Standards

|                     |                               |
|---------------------|-------------------------------|
| Flammability Rating | LSZH (Low Smoke Zero Halogen) |
|---------------------|-------------------------------|

## Operation/Application

|              |    |
|--------------|----|
| Halogen Free | No |
|--------------|----|

## Packaging Features

|                  |     |
|------------------|-----|
| Packaging Method | Bag |
|------------------|-----|

## Product Availability

|        |                                     |
|--------|-------------------------------------|
| Region | Asia   Australia/New Zealand   EMEA |
|--------|-------------------------------------|

## Product Type Features

|                         |                   |
|-------------------------|-------------------|
| Product Type            | Patch Cord        |
| System                  | AMP NETCONNECT    |
| Assembly Type           | Plug to Plug      |
| Connector Type (End A)  | RJ45 Modular Plug |
| Connector Type (End B)  | RJ45 Modular Plug |
| Performance Category    | Category 6        |
| Cable Assembly Category | Industry Standard |
| Shielded                | No                |

1-1711091-2

## Usage Conditions

---

Operating Temperature Range -20 – 60 °C

## Regulatory Compliance/Certifications

---

### Agency

RoHS 2011/65/EU

### Classification

Compliant