



60945-4

**PICABOND® Connector, 1000 loose piece, 400 Vdc, green**

- Lightweight, compact, and economical means of splicing multiconductor telephone cable
- No prestripping or cutting required, can tap without service interruptions, eliminates “turndowns”
- Color-coded to indicate size and type of wire; used for butt, straight, bridge and half-tap splicing applications

## Body Features

Cable Insulation Material	Air Core PIC   Paper or Pulp
Color Code	Green
Sealant	Unfilled

## Contact Features

Contact Base Material	Phosphor bronze
Contact Plating Material	Tin

## Dimensions

Wire Size (CMA)	26 – 22 AWG
-----------------	-------------

## Electrical Characteristics

Voltage Rating	400 Vdc
----------------	---------

## Packaging Features

Packaging Method	Loose Piece
Packaging Quantity	1000

## Product Availability

Region	Australia/New Zealand   EMEA   Latin America   North America
--------	--

## Product Type Features

Product Type	Splice
System	PICABOND
Splicing Applications	Bridge   Butt   Full Bridge   Half-tap   Straight (In-line)

## Usage Conditions

Operating Temperature	-40 – 60 °C
-----------------------	-------------

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant