






20 AMP, DOUBLE - POLE ELECTRO MECHANICAL SWITCH / BREAKER (3) PLACES


REAR VIEW



TOP VIEW




FRONT VIEW



PLUG
30 AMP, 250V x 3~ DELTA
TWIST LOCK
NEMA L15-30P

SIX (6)
RECEPTACLES
16 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19



SIDE VIEW

PANDUIT P/N	WEIGHT
P06B49M	4.9kg

NOTES:

- IDENTIFICATION:
 - UNIT TYPE: BASIC
 - ORIENTATION: HORIZONTAL, 1U
 - OUTLET QTY&TYPE: (6) C19
 - BREAKER QTY&TYPE: (3) 20AMP, DOUBLE-POLE
 - INPUT VOLTAGE: 200-240VAC, DELTA
 - INPUT CURRENT: 30A (24A DERATED)
 - INPUT PHASE: THREE-PHASE DELTA
 - RATED POWER: 8.6kVA
 - INPUT PLUG: NEMA L15-30P
 - INPUT CORD LENGTH: 3m [10']
- ACCESSORIES:
 - POCKET GUIDE
 - QTY: (4) M6 X 12 PAN HEAD MACHINE SCREWS
 - QTY: (4) M6 CAGED NUT
- RoHS COMPLIANT
- VISIT PANDUIT'S ON-LINE CATALOG AT WWW.PANDUIT.COM FOR ADDITIONAL PRODUCT INFORMATION CONTAINED IN THE SPECIFICATION SHEET AS WELL AS A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- MAXIMUM ALLOWABLE INPUT POWER = 8.6 kW
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN	
		DATE	
		PRINT	
TITLE BASIC SERIES PDU P06B49M CUSTOMER DRAWING			
ITEM REVISION NAME		PANDUIT	
DATASHEET FILE NAME			
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A	
THIRD ANGLE PROJECTION		DRAWING NUMBER: P06B49M_DC	
DRAWN BY JIANG	DATE 05/24/2017	CHK SEAN	SCALE NONE
REV		SHT 1 OF 1	
DATE		SCALE B	
BY			
CHK			
APR			
DESCRIPTION		ECN	