


NOTES:

- | | |
|--------------------|------------------------|
| UNIT TYPE: | BASIC |
| ORIENTATION: | VERTICAL, 0U FULL |
| OUTLET QTY&TYPE: | (36) C13, (6) C19 |
| BREAKER QTY&TYPE: | (3) 20AMP, DOUBLE-POLE |
| INPUT VOLTAGE: | 200-240VAC, DELTA |
| INPUT CURRENT: | 50A (28A DERATED) |
| INPUT PHASE: | THREE-PHASE DELTA |
| RATED POWER: | 10.0kVA |
| INPUT PLUG: | HUBBELL CS8365C |
| INPUT CORD LENGTH: | 3m [10'] |


- ADDITIONAL PRODUCT INFORMATION CONTAINED IN THE SPECIFICATION SHEET AS WELL AS A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART

6. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES



20 AMP, DOUBLE - POLE
— ELECTRO MECHANICAL
SWITCH / BREAKER (3) PLACES



WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY				SIGN DATE PRINT													
TITLE: BASIC SERIES PDU P42B28M CUSTOMER DRAWING																	
ITEM REVISION NAME:																	
DATASHEET FILE NAME:																	
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]				MATERIAL/COLOR: N/A													
 THIRD ANGLE PROJECTION				DRAWING NUMBER: P42B28M_DC													
Tolerance(mm) 0<L<200 ±0.5 200<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <th style="width: 15%;">DRAWN BY</th> <th style="width: 15%;">DATE</th> <th style="width: 15%;">CHK</th> <th style="width: 15%;">SCALE</th> <th style="width: 30%;">SHT 1 OF 1</th> <th style="width: 10%;">SCALE</th> </tr> <tr> <td>KUN</td> <td>05/24/2017</td> <td>SEAN</td> <td>NONE</td> <td></td> <td style="text-align: center; vertical-align: middle;">B</td> </tr> </table>				DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SCALE	KUN	05/24/2017	SEAN	NONE		B
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SCALE												
KUN	05/24/2017	SEAN	NONE		B												

REV	DATE	BY	CHK	APR	DESCRIPTION
-----	------	----	-----	-----	-------------

DESCRIPTION

ECN

	DRAWN BY	DATE
	KUN	(

BY	DATE
----	------

1	2
---	---

--	--

05/24/2017

CHK

05

SE

SCALE	
NONE	

Tolerance(mm)	
0<L≤200	±0.1
200<L≤500	±1.0
500<L≤1000	±2.0
1000<L≤2000	±4.0

SHT

3111

1 OF 1

SC

7

4