

2' x 2' TALKBACK LAY-IN CEILING SPEAKER MODEL V-CTLA-2

Technical Specification

FEATURES:

- EASY LAY-IN MOUNTING
- VOLUME SETTINGS
- SCUFF RESISTANT PERFORATED GRILLE
- DURABLE WHITE ACRYLIC BAKED ENAMEL FINISH
- INTEGRAL BACKBOX WITH THREE HOUR BURN RATING



DESCRIPTION:

This inconspicuous Lay-in Speaker can be installed in suspended ceilings in a minute. The speaker provides excellent music and voice reproduction. The integral backbox has a three hour burn test rating (UL181) and the rugged lightweight construction eliminates the need for support bars. The speakers white perforated grille blends into the ceiling by providing the appearance of a standard air return. The speaker assembly features a perforated steel grill finished with a durable white baked on acrylic enamel finish, and a 8" full range speaker with volume settings.

Specifications:

SPEAKER

8" (20.32 cm) Speaker

MAGNET WEIGHT

5 07.

MAGNET MATERIAL

Ceramic

VOICE COIL

45 ohm 3/4" (.34 cm) dia.

SOUND PRESSURE LEVEL

95 dB at 1 Meter on Axis With 1 Watt Input at 1 kHz

FREQUENCY RESPONSE

70 Hz to 17 kHz

POWER RATING

5 Watts Continuous

HOUSING AND FINISH

Steel housing with a white baked on acrylic enamel Finish

ENVIRONMENT

Temperature: 0 to 50 °C (32 to 122 °F)

DIMENSIONS AND WEIGHT

23.75 "L x 23.75 "L x 3.75 "D (60.325 cm x 60.325 cm x 9.525 cm)

Weight: 5.5 lbs (2.48 kg)

Shipping Weight: 14.0 lbs (6.3 kg) Packaged 2 per box



2' x 2' TALKBACK LAY-IN CEILING SPEAKER MODEL V-CTLA-2

Technical Specification

ARCHITECTS' AND ENGINEERS

The Model V-CTLA-2 Lay-in Ceiling Speaker shall consist of a white two foot by two foot perforated grille, a speaker and integral backbox. The volume setting is located in the back of the enclosure.

The speaker shall be 8" (20.32 cm) in diameter and have a 5 oz. ceramic magnet. The 8" speaker cone material shall be paper. The speaker impedance shall be 45 ohms. The diameter of the voice coil shall be 3/4" (.34 cm) diameter. The speaker shall be capable of handling 5 watts continuous power. Sound pressure level at 1 meter on axis with a 1 watt input shall be 95 dB. The frequency response shall be 70 Hz to 17 kHz.

The baffle shall be constructed with a single piece of perforated steel with a white baked on acrylic enamel finish. The backbox meets or exceeds A.S.T.M. E84 flame and smoke test and has a three hour burn rating (UL181).

Maximum dimensions of the grill shall be: 23.75 "L x 23.75 "L x 3.75 "D (60.325 cm x 60.325 cm x 9.525 cm). Weight shall be approximately 5.5 lbs (2.48 kg).

Limited Warranty

Valcom, Inc. warrants its products to be free from defects in materials and workmanship under conditions of normal use and service for a period of one year from the date of shipment. The obligation under this warranty shall be limited to the replacement, repair or refund of any such defective device within the warranty period, provided that:

- 1. inspection by Clarity indicates the validity of the claim,
- 2. the defect is not the result of damage, misuse, or negligence after the original shipment,
- 3. the product has not been in any way repaired by others and that factory sealed units are unopened. (A service charge plus parts and labor will be applied to units defaced or physically damaged).
- 4. freight charges for the return of products to Clarity are prepaid,
- 5. all units "out of warranty" are subject to a service charge. The service charge will cover minor repairs (major repairs will be subject to additional charges for parts and labor).

This warranty is in lieu of and excludes all other warranties expressed or implied, and in no event shall Valcom be liable for any anticipated profits, consequential damages, loss of time or other losses incurred by the buyer in connection with the purchase, operation or use of the product.

This warranty specifically excludes damage incurred in shipment. In the event a product is received in damaged condition, the carrier should be notified immediately. Claims for such damage should be filed with the carrier involved in accordance with the F.O.B. point.