

General Information

Extended Product Type:	F202 A-25/0,03
Product ID:	2CSF202101R1250
EAN:	8012542782506
Catalog Description:	F202 A-25/0,03 Residual Current Dev.
Long Description:	The RCCBs F200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous and selective AC and A types is completed with some configurations for special applications.

Categories

Products » Low Voltage Products and Systems » Modular DIN Rail Products » Residual Current Devices RCDs » Residual Current Devices RCDs

Ordering

Minimum Order Quantity:	1 piece
Customs Tariff Number:	85363030

Popular Downloads

Data Sheet, Technical Information:	2CSC400002D0209
------------------------------------	-----------------

Dimensions

Product Net Width:	0.035 m
Product Net Height:	0.085 m
Product Net Depth:	0.069 m
Product Net Weight:	0.200 kg

Technical

Standards:	IEC/EN 61008 UL 1053
Operating Characteristic:	Instantaneous
Type of Residual Current:	A type
Rated Residual Current:	30 mA
Rated Current (I_n):	25 A
Number of Poles:	2
Power Loss:	at Rated Operating Conditions per Pole 1 W
Rated Voltage (U_r):	230/400 V

Environmental

RoHS Status:	Following EU Directive 2011/65/EC
--------------	-----------------------------------

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	277 V AC
--------------------------------------	----------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	9AKK106713A5602
Instructions and Manuals:	2CSF423001D6406

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	0.041 m
Package Level 1 Height:	0.078 m
Package Level 1 Length:	0.096 m
Package Level 1 Gross Weight:	0.225 kg
Package Level 1 EAN:	8012542782506

Classifications

Object Classification Code:	Q
E-nummer:	2160114
ETIM 4:	EC000003 - Residual current circuit breaker (RCCB)
ETIM 5:	EC000003 - Residual current circuit breaker (RCCB)
ETIM 6:	EC000003 - Residual current circuit breaker (RCCB)

