

FH202 AC-25/0,03



Products Low Voltage Products and Systems Modular DIN Rail Products Residual Current Devices RCDs
Residual Current Devices RCDs

General Information

Extended Product Type:	FH202 AC-25/0,03
Product ID:	2CSF202006R1250
EAN:	8012542894209
Catalog Description:	FH202 AC-25/0,03 - Residual Current Dev.
Long Description:	The RCCBs FH200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous AC and A types is particularly suitable for installation in domestic applications.

Additional Information

Country of Origin:	Italy (IT)
Customs Tariff Number:	85363030
Data Sheet, Technical Information:	2CSC400002D0209
Declaration of Conformity - CE:	9AKK106713A5603
EAN:	8012542894209
ETIM 4:	EC000003 - Residual current circuit breaker (RCCB)
ETIM 5:	EC000003 - Residual current circuit breaker (RCCB)
ETIM 6:	EC000003 - Residual current circuit breaker (RCCB)
Environmental Information:	document not needed
Invoice Description:	FH202 AC-25/0,03 - Residual Current Dev.
Minimum Order Quantity:	1 piece
Number of Poles:	2
Object Classification Code:	Q
Operating Characteristic:	Instantaneous
Options Provided:	-
Package Level 1 EAN:	8012542894209
Package Level 1 Gross Weight:	0.225 kg
Package Level 1 Height:	0.078 m
Package Level 1 Length:	0.096 m
Package Level 1 Units:	1 piece
Package Level 1 Width:	0.041 m
Power Loss:	at Rated Operating Conditions per Pole 1 W
Product Main Type:	FH200
Product Name:	Residual Current Circuit Breaker
Product Net Depth:	0.069 m
Product Net Height:	0.085 m
Product Net Weight:	0.200 kg
Product Net Width:	0.035 m
Rated Current (I_n):	25 A
Rated Frequency (f):	50 ... 60 Hz
Rated Operational Voltage:	230 V AC
Rated Residual Current:	30 mA
RoHS Status:	Following EU Directive 2011/65/EC
Selling Unit of Measure:	piece
Short Description:	Residual Current Device - FH202 AC-25/0,03
Standards:	IEC 61008
Type of Residual Current:	AC type
Accessories Available:	No