


## MV-105 5KV Continuously Corrugated and Welded Aluminum Armor

### Product Description

Continuous aluminum armor  
EPR insulation  
133% insulation level

### Applications

Primary power and lighting circuits in manufacturing and processing plants, feeders in industrial and commercial distribution systems, power supply to station auxiliaries in electric power stations and substations. The MV-105 Cable may be used in wet/dry locations, conduits, ducts, troughs, trays or direct burial. Suitable for use in Class I, II, and III, Division 1 and 2 hazardous locations per NEC Articles 501, 502, and 503



### Specification

- CONDUCTOR: Bare Copper
- INSULATION: Ethylene Propylene Rubber (EPR), 133% Insulation Level
- OVERALL JACKET: Polyvinyl Chloride (PVC)
- VOLTAGE: 5kV

Part No.	Conductor Size (AWG)	No. of Conductors	Ground Wire Size (AWG)	No. of Strands	Diameter over Armor (in)	Diameter over Jacket (in)	Overall Jacket Thickness (in)	Color
7SS-0403	4	3	6	7	1.59	1.71	0.060	Yellow
7SS-0203	2	3	6	7	1.76	1.88	0.060	Yellow
7SS-1013	1/0	3	4	19	1.87	1.99	0.060	Yellow
7SS-2023	2/0	3	4	19	2.04	2.16	0.060	Yellow
7SS-4043	4/0	3	3	19	2.41	2.56	0.060	Yellow
7SS-3503	350 KCMIL	3	2	37	2.67	2.82	0.075	Yellow
7SS-5003	500 KCMIL	3	1	37	2.98	3.13	0.075	Yellow

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • [anixter.com](http://anixter.com)

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied. The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.