



## C-30-CPUSE-N-Ai6

**30 dB, Air Directional Coupler, 555–2700 MHz**

### General Specifications

Brand	Andrew®
Device Type	Coupler
Interface	N Female
Color	Silver

### Electrical Specifications

Operating Frequency Band	555 – 2700 MHz
3rd Order IMD	-160 dBc
3rd Order IMD Test Method	Two +43 dBm carriers
Average Power, maximum	200 W
Coupling	30.0 dB
Coupling Tolerance	±1.2 dB @ 698–2700 MHz   ±2.1 dB @ 555–698 MHz
Impedance	50 ohm
Insertion Loss at Frequency Band	0.2 dB @ 555–2700 MHz
Isolation at Frequency Band	50 dB @ 555–2700 MHz
Peak Power, maximum	1 kW
Reflected Power, maximum	200 W
Return Loss, minimum	20.8 dB
VSWR	1.2:1

### Mechanical Specifications

Coupling Nut Proof Torque	4.50 N-m   3.32 ft lb
Inner Contact Plating	Silver
Outer Contact Plating	Trimetal

### Environmental Specifications

Application	Indoor/Outdoor
Ingress Protection Test Method	IEC 60529:2001, IP65
Operating Temperature	-35 °C to +85 °C (-31 °F to +185 °F)
Relative Humidity	Up to 100%

### Dimensions

Height	22.00 mm   0.87 in
Length	155.00 mm   6.10 in
Width	75.00 mm   2.95 in
Net Weight	380.00 g   0.84 lb

C-30-CPUSE-N-Ai6

## Packed Dimensions

---

Height	40.0 mm		1.6 in
Length	180.0 mm		7.1 in
Width	90.0 mm		3.5 in
Shipping Weight	420.00 g		0.93 lb
Volume	648.0 cc		

## Regulatory Compliance/Certifications

---

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system